

# 2-POLE & 3-POLE SOCKETS & PLUGS



## Description

Members 2-Pole & 3-Pole sockets and plugs are often used to connect sources and controls for accessories or simple electrical applications across and within a trailer electrical system.

## Web Resources

Download installation instructions, 2D prints and technical resources at: [littelfuse.com/2-3-polesocketsplugs](http://littelfuse.com/2-3-polesocketsplugs)

## Features and Benefits

- Versions available with or without cap to protect against debris intrusion when not in use.
- Screw terminal versions especially suitable for spare & replacement parts markets.
- Mechanical resistance and watertightness guarantee an efficient and reliable electrical connection.

## Ordering Information

PART NUMBERS	DESCRIPTION	BODY MATERIAL	CABLE OUTLET	CABLE CORES ACCEPTED	STANDARD	NUMBER OF PINS	TERMINAL MATERIAL	TERMINALS	VOLTAGE
00680200	2P Socket	Nickel-Plated Brass	6mm	2x1.5mm <sup>2</sup>	ISO 4165	2	Tin-Plated Brass	Flat Terminals 6.3mm	12V   24V
00680600	2P Socket	Aluminum	6mm	2x1.5mm <sup>2</sup>	ISO 4165	2	Brass	Screw	12V   24V
00680700	2P Socket	Nickel-Plated Brass	6mm	1x1.5mm <sup>2</sup>	ISO 4165	2	Tin-Plated Brass	Flat Terminals 6.3mm	12V   24V
00680800	2P Socket	Nickel-Plated Brass	6mm	1x1.5mm <sup>2</sup>	ISO 4165	2	Brass	Screw	12V   24V
00680900	2P Socket	Nickel-Plated Brass	6mm	1x1.5mm <sup>2</sup>	ISO 4165	2	Tin-Plated Brass	Flat Terminals 6.3mm	12V   24V
00681000	2P Socket	Nickel-Plated Brass	6mm	1x1.5mm <sup>2</sup>	ISO 4165	2	Brass	Screw	12V   24V
00681100	2P Socket	Nickel-Plated Brass	6mm	2x1.5mm <sup>2</sup>	ISO 4165	2	Tin-Plated Brass	Flat Terminals 6.3mm	12V   24V
00681200	2P Socket	Nickel-Plated Brass	6mm	2x1.5mm <sup>2</sup>	ISO 4165	2	Tin-Plated Brass	Flat Terminals 6.3mm	12V   24V
00681300	2P Socket	Nickel-Plated Brass	6mm	2x1.5mm <sup>2</sup>	ISO 4165	2	Brass	Screw	12V   24V
00682000	2P Socket	Plastic	6mm	2x1.5mm <sup>2</sup>	ISO 4165	2	Ni-Plated Brass + Ni-Plated bronze	Flat Terminals 6.3mm	12V   24V
00680300	2P Plug	Plastic	6mm	2x1.5mm <sup>2</sup>	ISO 4165	2	Brass + Bronze	Flat Terminals 6.3mm	12V   24V
00680400	2P Plug	Plastic	6mm	1x1.5mm <sup>2</sup>	ISO 4165	2	Brass + Bronze	Screw	12V   24V
00681500	2P Plug	Plastic	6mm	2x1.5mm <sup>2</sup>	ISO 4165	2	Brass	Screw	12V   24V
00681800	3P Plug	Plastic	8-13mm	5x1.5mm <sup>2</sup>	DIN 9680	3	Tin-Plated Copper	Flat Terminals 6.3mm	12V
00681600	3P Socket	Plastic	8-13mm	5x1.5mm <sup>2</sup>	DIN 9680	3	Tin-Plated Copper	Flat Terminals 6.3mm	12V
00681700	3P Socket	Plastic	8-13mm	5x1.5mm <sup>2</sup>	DIN 9680	3	Tin-Plated Copper	Flat Terminals 6.3mm	12V