



PART No.	BODY	BODY STYLE	FUSE PROVIDED	FUSE RATING	REMARKS	
0FNYY0001Z	0FNYY0001Z	1	NONE	----	NOTE 1	
0FNYY0004Z	0FNYY0001Z	1	0307004.Z	4 AMP	NOTE 1	
0FNYY0006Z	0FNYY0001Z	1	0307006.Z	6 AMP	NOTE 1	
0FNYY0075Z	0FNYY0001Z	1	0307075.Z	7.5 AMP	NOTE 1	Obs.
0FNYY0009Z	0FNYY0001Z	1	0307009.Z	9 AMP	NOTE 1	Obs.
0FNYY0014Z	0FNYY0001Z	1	0307014.Z	14 AMP	NOTE 1	
0FNYY0020Z	0FNYY0001Z	1	0307020.Z	20 AMP	NOTE 1	
0FNYY0030Z	0FNYY0030Z	2	0307030.Z	30 AMP	NOTE 2	



NOTES:

1. FOR OFNY0001:
 - A) MAX. RATING: 20 AMPS, 32 VOLTS AT A MAXIMUM OPERATING TEMPERATURE OF 180° F (82° C).
 - B) BODY MATERIAL: NYLON 6/6, BLACK
KNOB MATERIAL: NYLON 6/6, BLACK
SPRING MATERIAL: COATED STEEL
CONTACT RIVET MATERIAL: BRASS
WIRE LEAD MATERIAL: #14 GAUGE, STRANDED, BLACK
 - C) FUSEHOLDER IS SHIPPED WITH KNOB AND BODY ASSEMBLED (FUSE INSTALLED, IF REQUIRED) FORMING A LOOP.
2. FOR OFNY0030:
 - A) MAX. RATING: 30 AMPS, 32 VOLTS AT A MAXIMUM OPERATING TEMPERATURE OF 180° F (82° C).
 - B) BODY MATERIAL: NYLON, WHITE TRANSLUCENT
KNOB MATERIAL: NYLON 6/6, BLACK
SPRING MATERIAL: COATED STEEL
CONTACT RIVET MATERIAL: BRASS
WIRE LEAD MATERIAL: #12 GAUGE, STRANDED, ORANGE PVC, G.P. SAE TYPE 1
 - C) FUSEHOLDER IS SHIPPED WITH KNOB AND BODY ASSEMBLED (FUSE INSTALLED).

GENERAL NOTES:

1. TOTAL WEIGHT OF SHIPPING CARTON SHALL BE LIMITED TO 50 LBS. MAX.

	NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
	BILL OF MATERIAL				
	COPIES TO		MATL SPEC	FINISH	
	1	9 18	DRW JMB	DATE 2/11/99	SCALE 1=1
	2	10 19	CHK	DATE	SUPER DRW
	3	12 20			
	4	13 21	APPD	DATE	RAW STK WT LBS/M
	5	14 23			
	6	15 33			TOLERANCE UNLESS OTHERWISE SPECIFIED
	7	16 43			TWO PLACE DEC ±.01 FRACTION ±
	8	17 53			THREE PLACE DEC ±.005 ANGULAR ±1°
	TITLE		FUSEHOLDER, IN LINE (FUSE OPTIONAL)		
	LTR	REVISION			CHK APD
F	38728C- REVISE & REDRAW ON NEW FORMAT 2/26/99 JMB				
				DWG. NO. SERIES OUTLINE G	OFNY0000Z

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.	
	NOTES CRITICAL CHARACTERISTICS.
(C)	DENOTES CPK DIMENSIONS--MINIMUM CPK VALUE
(S)	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN TYPULSE INSPECTION INSTRUCTIONS.
	DIMENSIONS CP DIMENSIONS--MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.
G	82904C - OBS. OFNY00075Z, OFNY00009Z
I	3/21/03 BJJ