

Ø20.7 ± 0.18  
[Ø0.813 ± 0.007]

3.2 ± 0.08  
[0.125 ± 0.003]

8.7 ± 0.13  
[0.343 ± 0.005]

57.1 ± 1.60  
[2.250 ± 0.063]

63.5 ± 1.60  
[2.500 ± 0.063]

41.3 ± 1.60  
[1.625 ± 0.063]

81.0 ± 1.60  
[3.188 ± 0.063]

18.3 ± 0.25  
[0.720 ± 0.010]

# REVISION

REV	DATE	DESCRIPTION
A	7/6/23	526696GCP - RELEASE MRY

1				
NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M

## BILL OF MATERIAL

<S>	CRITICAL CHARACTERISTIC FOR PART SAFETY/COMPLIANCE
●	DENOTES CRITICAL CHARACTERISTICS.
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS.
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.

A

MATL SPEC		FINISH	
DRW JMoler	DATE 6/22/2023	SCALE NTS	FINISH GOOD WT GRAMS/PIECE

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [ ] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994



TITLE L50S 35-60A OUTLINE



REVISION	DRWG NO.	SHEET 1 OF 1
A	OL-L50S060	