




PART NUMBER	COLOR	DIM "A"	DIM "B"	DIM "C"	THREAD "D"	NUT TYPE	STUD CAPS INCLUDED
JBPT0001Z	RED	0.75 (19.05)	0.75 (19.05)	0.75 (19.05)	3/8"-16	DOUBLE NUT	YES
JBPT0002Z	BLACK	0.75 (19.05)	0.75 (19.05)	0.75 (19.05)	3/8"-16	DOUBLE NUT	YES
JBPT0001Z-NC	RED	0.75 (19.05)	0.75 (19.05)	0.75 (19.05)	3/8"-16	HEX FLANGE NUT	NO
JBPT0002Z-NC	BLACK	0.75 (19.05)	0.75 (19.05)	0.75 (19.05)	3/8"-16	HEX FLANGE NUT	NO
JBPT0003Z	RED	1.05 (26.67)	0.65 (16.51)	1.05 (26.67)	1/2"-13	DOUBLE NUT	YES
JBPT0004Z	BLACK	1.05 (26.67)	0.65 (16.51)	1.05 (26.67)	1/2"-13	DOUBLE NUT	YES
JBPT0003Z-NC	RED	1.05 (26.67)	0.65 (16.51)	1.05 (26.67)	1/2"-13	HEX FLANGE NUT	NO
JBPT0004Z-NC	BLACK	1.05 (26.67)	0.65 (16.51)	1.05 (26.67)	1/2"-13	HEX FLANGE NUT	NO
JBPT13802Z2R-NC	RED	1.25 (31.75)	0.75 (19.05)	0.75 (19.05)	3/8"-16	HEX FLANGE NUT	NO
JBPT13802Z2B-NC	BLACK	1.25 (31.75)	0.75 (19.05)	0.75 (19.05)	3/8"-16	HEX FLANGE NUT	NO

LTR	DATE	REVISION	CHK	APD
D	11/4/11	503599ERA-SEE ERN GMB		

Ø 1.312 [33,325]




1.130 [28,702]
1.125 [28,575]



(SHOWN WITHOUT STUD CAPS OR NUTS INSTALLED)

NOTES:

- ALL DIMENSIONS ARE FOR REFERENCE ONLY.
- MOUNTING THREADS ARE 1"-11½ NPSM
- MAXIMUM MOUNTING TORQUE-10 FT. LBS.
- MAXIMUM TORQUE ON 3/8-16 STUDS-40 FT.LBS.
MAXIMUM TORQUE ON 1/2-13 STUDS-40 FT.LBS.
PART TO BE RESTRAINED DURING TORQUE PROCEDURE
- PARTS SUPPLIED WITH TWO NUTS & PLASTIC LOCKNUT.
STUD CAPS SUPPLIED EXCEPT FOR PARTS WITH "-NC" SUFFIX.



-				
-				
-				
NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.				
⊙	DENOTES CRITICAL CHARACTERISTICS.			
CPK	DENOTES CPK DIMENSIONS. -MINIMUM CPK VALUE			
(ST)	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS			
CP	DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE			
MATL SPEC				
COPIES TO				
1	9	18		
2	10	19		
3	12	20		
4	13	21		
5	14	23		
6	15	33		
7	16	43		
8	17	53		
FINISH				
DRW	CAD	DATE	03/23/09	SCALE 1.5:1
CHK		DATE		SUPER DR
APPD		DATE		FINISH GOOD WT
GRAMS/PIECE				
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-MH)				
DIMENSION	0.5 - 3	3 - 6	6 - 30	30 - 120
TOLERANCE	±0.13	±0.25	±0.38	±0.63
2ND ANGLE PROJECTION				
TITLE	PASS-THRU JUNCTION BLOCKS			
	3/8"-16 & 1/2"-13			
LITTELFUSE				
DES PLAINES, ILLINOIS 60016			REVISION DRWG. NO.	
			OUTLINE	
			D OL-JBPT0000Z	

CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED