



NOTES:

1. STANDING FLASH 0.025 MAXIMUM PERMISSIBLE AT PARTING LINE.
2. STANDING FLASH 0.010 MAXIMUM PERMISSIBLE ALL OTHER AREAS.
3. MATERIAL SPECIFICATION:
HIGH CONSISTENCY RUBBER (HCRP)
4. CAVITY NUMBER AND MOLDING GATES PERMITTED ON THIS SURFACE. MAXIMUM HEIGHT 0.007.



868-096	GRAY	.173 DIA
868-095	BLUE	.115 DIA
PART NO	COLOR	DIA ^o "A"

NO		COMPONENT NO		DESCRIPTION		QTY/M		U/M	
BILL OF MATERIAL									
A		COPIES TO		MATL SPEC		SEE NOTE 3		FINISH	
		1	9 18	DRW	DWM	DATE	05/23/08	SCALE	2 : 1
		2	10 19						
		3	12 20	CHK		DATE		SUPER DRW	
		4	13 21						
		5	14 23	APPD		DATE		RAW SIK WT	LBS/M
		6	15 33						
		7	16 43	TOLERANCE UNLESS OTHERWISE SPECIFIED					
		8	17 53	TWO PLACE DEC. ±.01					
				THREE PLACE DEC. ±.005					
				ANGULAR ±1°					
TITLE			SEAL FUSE HOLDER						
			SPLASH-PROOF MAXI FUSE HOLDER						
						REVISION		DRAWG. NO.	
		DES PLAINES, ILLINOIS 60016				A		868-095 868-096	
						CHK		OUTLINE	
						APD			
		000402ER - RELEASED							
		05/23/08				DWM			

	UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.
0	DENOTES CRITICAL CHARACTERISTICS.
CPK	DENOTES CPK DIMENSIONS.-MINIMUM CPK VALUE
(S)	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE AND IS THE BASIS FOR MEASUREMENT AND TOLERANCE ANALYSIS.
(T)	DENOTES INSPECTOR MUST USE INTELLECT TO INSPECT ON INSTRUCTIONS.
CP	DENOTES CP DIMENSIONS.-MINIMUM CP VALUE
CP _{MIN}	MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SPECIFIED FOR THE DIMENSIONALLY LOCATED TO AVOID FOR MAXIMUM TOOL LIFE.