



SPECIFICATIONS:

VOLTAGE RATING: 600Vac/dc

AMP RATING: 30A

INTERRUPT RATING: 200kA

WIRE RANGE: 0.75-10mm²
18-4 AWG

SUGGESTED TORQUE: (1) 0.75-25mm² 2.0-2.5 Nm
18-8 AWG 18-22 lb-in
(2) 0.75-10mm² 2.0-2.5 Nm
18-6 AWG 18-22 lb-in
(1) 6-4 AWG 22-26 lb-in

APPROVALS: UL Listed (E14721)
CSA Certified

| REVISION | | |
|----------|---------|-------------------------|
| REV | DATE | DESCRIPTION |
| A | 10/3/22 | 525710GCP - RELEASE MRY |

| 1 | | | | |
|----|--------------|-------------|-------|-----|
| NO | COMPONENT NO | DESCRIPTION | QTY/M | U/M |

BILL OF MATERIAL

| | |
|-----|--|
| <S> | CRITICAL CHARACTERISTIC FOR PART SAFETY/COMPLIANCE |
| ● | DENOTES CRITICAL CHARACTERISTICS. |
| CPK | DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE |
| ⬡ | DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS. |
| CP | DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE. |

A

| | |
|-----------|--------|
| MATL SPEC | FINISH |
|-----------|--------|

| | | | |
|---------------|-------------------|--------------|-------------------------------|
| DRW JMOLER | DATE 9/23/2022 | SCALE NTS | FINISH GOOD WT GRAMS/PIECE |
|---------------|-------------------|--------------|-------------------------------|

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994

| | |
|-------------------------|--|
| 3RD ANGLE PROJECTION | |
|-------------------------|--|

TITLE LFPSC001 OUTLINE

| | | | |
|--|----------------------|--------------------------------|---------------------|
| Littelfuse CHICAGO, ILLINOIS 60631 | REVISION A | DRWG NO. OL-LFPSC001 | SHEET 1 OF 1 |
|--|----------------------|--------------------------------|---------------------|