

MM.	IN
.50	.020
3.80	.149
6.40	.251
7.14	.281
7.54	.296
9.70	.381
14.00	.551
19.60	.771
20.60	.811
28.40	1.118
31.80	1.251
44.20	1.740
44.70	1.759
52.58	2.070
54.10	2.129
28.40	1.118

7762

$\frac{7.14}{764}$ DIA HOLE (2 PLACES)

- BUTTON, ZINC PLATE

CASE


9.70 TRAVEL

Technical drawing of a mechanical part with dimensions:

- Top diameter: 20.60 DIA
- Top section height: 54.10
- Bottom section height: 52.58
- Bottom section width: 19.60
- Bottom section height: 6.40
- Left section height: 28.20
- Left section width: 14.00
- Left section label: RAVEL

NOTE:
ALL STEEL PARTS PLATED

METRIC

													DO NOT SCALE	
LET.	WAS	DATE	BY	LET	WAS	DATE	BY	MATERIAL	DRAWN	CHECKED	APPRV'D	SCALE		DATE DRAWN
									DPS	AF		1=1		5-11-81
								FINISH	  Cole Hersee Co. 20 OLD COLONY AVENUE SOUTH BOSTON MA U.S.A. 02127					DATE BLUEPRINT
								TOLERANCES	DIMMER SWITCH					7762
								DECIMAL ± METRIC ±						
					C REDRAWN	8-28-81	RD							