


4

3

2

1



NOTES:

1. SILVER CONTACT SURFACES
2. ALL STEEL PARTS PLATED
3. ALL DIMENSIONS REF. ONLY
4. PARTS MAY BE ASSEMBLED OR SUPPLIED IN A BAG
5. RATING:
CONTINUOUS - 175 AMPS 6-12-24-36 V DC
INTERMITTENT-1000 AMPS MAX 6-12-24-36 V DC 15 SECONDS 'ON' 5 MINUTES 'OFF'
6. TORQUE SPECIFICATIONS:
MOUNTING STEM NUTS: 20 FT LBS [27 N.m] MAX
3/8" NUTS 70-90 IN LBS [8-10 N.m]

(AA)

Revision Control Record

Rev.	Description of Change	ECN No.	Date	Rev.	Description of Change	ECN No.	Date	Tolerances	Unless otherwise specifically noted, the following are default tolerances:	PROPRIETARY INFORMATION	Special Characteristics:	Cole Hersee Co.
AA	REVISED NOTES	08680	11/24/08					2-places +/- 0.02"	3-places +/- 0.005"	Angular +/- 1°	☒ Critical Characteristic, relating to Safety and/or Regulatory Compliance ☒ Significant Characteristic relating to Process Control ☒ Control Dimension relating to Form - Fit - Function as defined by Cole Hersee Company and/or the Customer	20 Old Colony Ave., South Boston, MA, 02127 Phn: 617-268-2100 Web: www.colehersee.com
								Metric: Shown in [] refers to equivalent English Dim Tol				
								"REF." or an Asterisk (*) = Non-Toleranced Reference Dimension, shown for clarification purposes only.				
								NOTE: All tolerances are Non-Cumulative.				
								FORM CHT-6 (2/07)	Used On or Ref.:	Scale: 1:1	Drawn BY: PJS	Date Drawn: 12/27/55
												Pg. 1 of 1



Cole Hersee Co.

20 Old Colony Ave., South Boston, MA, 02127
Phn: 617-268-2100 Web: www.colehersee.comDescription: **SWITCH, MASTER DISCONNECT**Drawing / Part No.: **2484-A** Current Rev.: **AA**

4

3

2

1