

Ø27.1 ± 0.18
[Ø1.07 ± 0.007]

3.2 ± 0.08
[0.13 ± 0.003]

10.3 ± 0.13
[0.41 ± 0.005]

103.4 ± 1.57
[4.07 ± 0.062]

127.0 ± 1.57
[5.00 ± 0.062]


92.7 ± 1.57
[3.65 ± 0.062]

73.8 ± 1.57
[2.91 ± 0.062]

19.1 ± 0.20
[0.75 ± 0.008]

REVISION

REV	DATE	DESCRIPTION
A	6/19/23	526604GCP - RELEASE MRY

1					
NO	COMPONENT NO	DESCRIPTION		QTY/M	U/M
BILL OF MATERIAL					
<S>		CRITICAL CHARACTERISTIC FOR PART SAFETY/COMPLIANCE			
●		DENOTES CRITICAL CHARACTERISTICS.			
CPK		DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE			
⬡ST		DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS.			
CP		DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.			A
MATL SPEC			FINISH		
DRW JMoler		DATE 5/25/2023		SCALE NTS	FINISH GOOD WT GRAMS/PIECE
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994					
3RD ANGLE PROJECTION					
TITLE KLC 70-100A OUTLINE					
 Littelfuse® CHICAGO, ILLINOIS 60631		REVISION A		DRWG NO. OL-0KLC100	
				SHEET 1 OF 1	