




THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.

REVISIONS					
REV.	DESCRIPTION	DATE	GCF / ECR	DESIGNED	APPROVED
A	Initial Release	30-Jan-23		L.Dal Molin	M.Tinto



PRESCRIPTION


£: Mold code

\$: Molding footprint number

&: Manufacture date

*: Material symbol

1	Protection ext. 4 holes	Polyamide	1
POS.	DESCRIPTION	MATERIAL	Q.ty

DIMENSIONS AND TOLERANCES IN MILLIMETERS, DEFINED ACCORDING TO ISO 1101-2017.							
linear dimensions							
0,5 3	>3 6	>6 30	>30 120	>120 400	>400 1000	>1000 2000	
±0,2	±0,3	±0,5	±0,8	±1,2	±2	±3	
angle (for range of lengths)							
up to 10		>10 50		>50 120		>120 400	
±1°30'		±1°		±0°30'		±0°15'	
	FIT/ FUNCTION CRITICAL CHARACTERISTICS SYMBOL						
<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL						
CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE						
	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS						
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE						
		NAME	DATE		 Littelfuse® Expertise Applied Answers Delivered		
DRAWN		L.Dal Molin	30 Jan 2023				
CHECKED		-	-				
		-	-				
FORM NO.: CVP-PE40-0013 REV A				TITLE PROTECTION EXTERNAL 4 HOLES			
FIRST ANGLE PROJECTION							
				SIZE:	DWG. NO.	OUTLINE	REV.
DO NOT SCALE DRAWING				A3	OL-00902800	2800	A
SCALE 1:1				SHEET 1 OF 1			