



SPECIFICATIONS:

VOLTAGE RATING: 600V

AMP RATING: 30 AMPERES

INTERRUPT RATING: 200kA

WIRE RANGE: 0.75-50mm²
#18-1 AWG
Cu ONLY

SUGGESTED TORQUE: 0.75-1mm² 2.5Nm
1.5-50mm² 4Nm
#18-1 AWG 35 lb-in

APPROVALS: UL LISTED (FILE NO. E14721)
CSA CERTIFIED (FILE NO. 256018)

REVISION				
REV	DATE	DESCRIPTION		
A	10/13/22	525731GCP - RELEASE MRY		