


PART NUMBER	"A"	"B"	"C"	"D"	LEAD "A" COLOR	LEAD "B" COLOR	WITH FUSE
OFHM0001ZXJA	150±5 [5.91±0.2]	150±5 [5.91±0.2]	NO END STRIP	NO END STRIP	RED	RED	3A
OFHM0001ZXJB	150±5 [5.91±0.2]	150±5 [5.91±0.2]	NO END STRIP	NO END STRIP	BLUE	BLUE	3A

LTR	DATE	REVISION	CHK	APD
A	5/Aug/16	516235ECC-NEW RELEASE FYUE		



IN-LINE FUSEHOLDER SHOWN
WITH MINI FUSE INSTALLED
(NOT INCLUDED)

- NOTES:
- HOLDER MATERIAL: BLACK TPV
 - CONTACTS: COPPER ALLOY: TIN-PLATED
 - WIRE: 20 AWG UL1015 WIRE
 - CRIMP: MUST MEET SAE/USCAR 21 STANDARD
 - RATING: 3A, 32Vdc
 - FUSEHOLDERS SHOULD NOT BE PLACED UNDER TENSION IN FINAL APPLICATION
 - MAX TEMPERATURE 105°C

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES			
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.			
⊙	DENOTES CRITICAL CHARACTERISTICS.		
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE		
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS		
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE		
COPIES TO	MATL SPEC SEE NOTES		
1 9 18	FINISH SEE NOTES		
2 10 19			
3 12 20			
4 13 21	DRW FYUE	DATE 05/Aug/16	SCALE 1:1
5 14 23	CHK	DATE	SUPER DR
6 15 33	APPD	DATE	FINSH GOOD WT
7 16 43			GRAMS/PIECE
8 17 53			
TOLERANCE UNLESS OTHERWISE SPECIFIED ONE PLACE DEC +/- .3 THREE PLACE DEC +/- .100 TWO PLACE DEC +/- .15 ANGULAR +/- 1°			
3RD ANGLE PROJECTION	TITLE MINI IN-LINE FUSEHOLDER		
Littelfuse		REVISION A	DRWG. NO. OFHM0004ZXJ
DES PLAINES, ILLINOIS 60016		OUTLINE	

METRIC

CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED