

Ø38.1 ± 0.18
[Ø1.500 ± 0.007]

6.4 ± 0.08
[0.250 ± 0.003]

10.3 ± 0.13
[0.406 ± 0.005]

58.0 ± 1.60
[2.282 ± 0.063]

73.8 ± 1.60
[2.906 ± 0.063]


40.5 ± 1.57
[1.594 ± 0.062]

97.6 ± 1.60
[3.844 ± 0.063]

25.3 ± 0.25
[0.995 ± 0.010]

REVISION

REV	DATE	DESCRIPTION
A	6/27/23	526654GCP - RELEASE MRY

1					
NO	COMPONENT NO	DESCRIPTION		QTY/M	U/M
BILL OF MATERIAL					
<S>	CRITICAL CHARACTERISTIC FOR PART SAFETY/COMPLIANCE				
●	DENOTES CRITICAL CHARACTERISTICS.				
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE				
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS.				
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.				
MATL SPEC			FINISH		
DRW JMoler		DATE 6/20/2023		SCALE NTS	FINISH GOOD WT GRAMS/PIECE
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994					
3RD ANGLE PROJECTION					
TITLE L25S 225-700A OUTLINE					
 Littelfuse® CHICAGO, ILLINOIS 60631		REVISION A		DRWG NO. OL-L25S700	
				SHEET 1 OF 1	