





THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.

REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	PCO #5300044. INITIAL RELEASED. DSILVA	4/21/2022	L.ARGIL





NOTES: (UNLESS OTHERWISE SPECIFIED)

1. NOTES:
- 1.1. #14 GXL WIRE LEADS NOM. O.D. .122 COLOR: RED.
1.2. HOLDER AND COVER MATERIAL: BLACK PVC.
1.3. CONTACTS: COPPER ALLOY.
1.4. MAX. RATING: 20 AMPS, 58Vdc.

TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-FH)													
.5 to 3	>3 to 6	>6 to 30	>30 to 120	>120 to 400									ANGLE
±0.10	±0.10	±0.20	±0.30	±0.50									NONE

DIMENSIONS ARE SHOWN IN MILLIMETERS. DIMENSIONS AND TOLERANCES ARE DEFINED ACCORDING TO ANSI/ASME Y14.5-1994.

PER CH1-NPD20-0008 PROCEDURE		FIT/ FUNCTION CRITICAL CHARACTERISTICS
	<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL
	CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE
	ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS
	CP	DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

	NAME	DATE	 Littelfuse Expertise Applied Answers Delivered		
DRAWN	DSILVA	4/13/2022			
CHECKED	-	-			
	-	-			
	-	-	TITLE MINI IN-LINE HOLDER W/ TERMINAL		
FORM NO: CVP-PE40-0003 REV B					
THIRD ANGLE PROJECTION					
					
			SIZE B	DWG. NO. OL-0FHM0001ZXJ-T	REV. A
DO NOT SCALE DRAWING			SCALE 1:1		SHEET 1 OF 1

mm
[in]