





REVISIONS				
REV.	DESCRIPTION	DATE	DESIGNED	APPROVED
A	First issue of outline drawing	22-May-20	L.Dal Molin	M.Tinto



SCALE 1:1

8	Key no logo red complete		1	EA
7	Eyelet	Iron	1	EA
6	Nut M10	Brass	4	EA
5	Spring washer	Bronze	2	EA
4	Washer 10.3x18x2		2	EA
3	Upper body cam double	Polyamide	1	EA
2	Power stud M10	Copper	2	EA
1	Lower body M10 cont.-holder hole	Polyamide	1	EA
POS.	DESCRIPTION	MATERIAL	QTY.	U/M



CLOSED CONTACT

OPEN CONTACT

PLUGGING IN-PULL OUT KEY

CHARACTERISTICS AND PRESCRIPTIONS

- Nominal voltage: 24V max
- Maximum continuos current: 150A
- Maximum current: 1000A for 5sec at 25°C
- Maximum short time current: 450A for 4.5 minutes
- Tightening torque M10 nuts ref. 7 ± 1Nm

SAP drawing number:

Material and treatments:

DIMENSIONS AND TOLERANCES IN MILLIMETERS. DEFINED ACCORDING TO ISO 1101-2017.						
linear dimensions						
0,5 3	>3 6	>6 30	>30 120	>120 400	>400 1000	>1000 2000
±0,2	±0,3	±0,5	±0,8	±1,2	±2	±3
angle (for range of lengths)						
up to 10	>10 50	>50 120	>120 400	>400 1000	>1000 2000	>2000 4000
±1°30'	±1°	±0°30'	±0°15'	±0°15'	±0°15'	±0°15'
●	FIT/ FUNCTION CRITICAL CHARACTERISTICS SYMBOL					
<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL					
CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE					
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS					
CP	DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE					
	NAME	DATE	 Expertise Applied Answers Delivered			
DRAWN	L. Dal Molin	05-Apr-19				
CHECKED	-	-				
	-	-				
			TITLE			
			BATTERY MAIN SWITCH IGC-150 (N°2 M10)			
FORM NO:	CVP-PE40-0013 REV A					
FIRST ANGLE PROJECTION						
SIZE:	A2	DWG. NO.	OL-08098780	OUTLINE REV.	A	
DO NOT SCALE DRAWING	SCALE 1:1			SHEET 1 OF 1		