



THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.

ART. NR.	DESCRIPTION
178.6152.2501	FKH-HOLDER WITH LOOP 2,5mm^2




NOTES:

MATERIAL:

1. FKH HOLDER: THERMOPLASTIC
2. ATO CONTACTS TERMINALS: COPPER ALLOY
3. SHRINK TUBING: HEAT SHRINKABLE POLYMER
4. LEAD WIRE-YELLOW: COPPER

REVISIONS



ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	PCO #5300128. INITIAL RELEASE. DSILVA.	11/7/2022	L.ARGIL





4	-	SHRINK TUBING	2	EA
3	-	LEAD WIRE - YELLOW	1	EAD
2	-	ATO CONTACT TERMINAL	2	EAD
1	-	FKH-HOLDER	1	EAD
NO.	COMPONENT NO.	COMPONENT NAME	QTY/M	U/M

TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-mK)									
.5 to 3	>3 to 6	>6 to 30	>30 to 120	>120 to 400					ANGLE
±0.10	±0.10	±0.20	±0.30	±0.50					NONE

DIMENSIONS ARE SHOWN IN MILLIMETERS. DIMENSIONS AND TOLERANCES ARE
DEFINED ACCORDING TO ANSI/ASME Y14.5-1994.

PER CH1-NPD20-0008 PROCEDURE		FIT/ FUNCTION CRITICAL CHARACTERISTICS
	<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL
	CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE
		DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMANTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS
	CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

	NAME	DATE	 Littelfuse® Expertise Applied Answers Delivered	
DRAWN	DSILVA	9/27/2022		
CHECKED	-	-		
	-	-		
FORM NO: CVP-PE40-0003 REV B THIRD ANGLE PROJECTION			TITLE HOLDER FKH (ATO) W/ WIRE LOOP 2.5MM2	
			SIZE B	DWG. NO. OUTLINE
DO NOT SCALE DRAWING			OL-178.6152.2500	REV. A
SCALE 1:1			SHEET 1 OF 1	