





REVISIONS					
REV.	DESCRIPTION	DATE	GCF / ECR	DESIGNED	APPROVED
A	Initial Release	18-Jul-22		L.Dal Molin	M.Tinto



- PREScriptions
- Torque of screw M10=19 Nm max
 - Fix the device with M6 screw and with torque of 6±2 Nm

- CHARACTERISTICS
- Nominal working tension: 12-24V
 - Nominal working current main contact: 250A
 - Nominal max current main contact: 2000A for 5sec.
 - Number of mechanical operations: 150.000
 - Number of electrical operations: 50.000

DIMENSIONS AND TOLERANCES IN MILLIMETERS, DEFINED ACCORDING TO ISO 1101-2017.								
linear dimensions								
0,5 3	>3 6	>6 30	>30 120	>120 400	>400 1000	>1000 2000		
±0,2	±0,3	±0,5	±0,8	±1,2	±2	±3		
angle (for range of lengths)								
up to 10		>10 50		>50 120		>120 400		
±1°30'		±1°		±0°30'		±0°15'		
	FIT/ FUNCTION CRITICAL CHARACTERISTICS SYMBOL							
<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL							
CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE							
	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS							
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE							
NAME		DATE		 <div>Littelfuse®</div> <div>Expertise Applied Answers Delivered</div>				
DRAWN		L. Dal Molin					18-Jul-22	
CHECKED		-					-	
		-					-	
FORM NO: CVP-PE40-0013 REV A				TITLE				
FIRST ANGLE PROJECTION				TGC/MGE-MS7 +/- 12-24V				
				SIZE: A3	DWG. NO. OL-08075163	OUTLINE REV. A		
DO NOT SCALE DRAWING				SCALE 1:2		SHEET 1 OF 1		

