

**SPECIFICATIONS:**

**VOLTAGE RATING:** 600V

**AMP RATING:** 30 AMPERES



**INTERRUPT RATING:** 200kA

**WIRE RANGE:** 0,75-50mm<sup>2</sup>  
#18-1 AWG  
Cu ONLY

**SUGGESTED TORQUE:** 0,75-1mm<sup>2</sup> 2.5Nm  
1,5-50mm<sup>2</sup> 4Nm  
#18-1 AWG 35 lb-in

**APPROVALS:** UL LISTED (FILE NO. E14721)  
CSA CERTIFIED (FILE NO. 256018)

REVISION		
REV	DATE	DESCRIPTION
A	10/3/22	525720GCP - RELEASE MRY
B	11/9/22	525900ECP/D - CHANGE \$18-1 AWG TORQUE MRY

1				
NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
<b>BILL OF MATERIAL</b>				
<S>	CRITICAL CHARACTERISTIC FOR PART SAFETY/COMPLIANCE			
●	DENOTES CRITICAL CHARACTERISTICS.			
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE			
ⓈT	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS.			
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.			<b>B</b>
MATL SPEC		FINISH		
DRW JMOLER	DATE 9/26/2022	SCALE NTS	FINISH GOOD WT  GRAMS/PIECE	
UNLESS OTHERWISE SPECIFIED, DIMENSTIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [ ] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994				
3RD ANGLE PROJECTION 				
<b>TITLE</b>  LFPSJ303 OUTLINE				
 <b>Littelfuse®</b> CHICAGO, ILLINOIS 60631		REVISION  <b>B</b>	DRWG NO.  <b>OL-LFPSJ303</b>	SHEET 1 OF 1