







- Number of electrical and mechanical operations: 100.000
- Tightening torque nuts M10/M12: 20 Nm
- Tightening torque nuts M5/M: 2 Nm

- Nominal voltage range: 12 - 24 V
- Maximum continuous current on main contacts: 250 A at 23°C
- Maximum short time current on main contact: 2000 A for 30 sec. at 23°C


- (*): Manufacturing date
- (\$): Label to be placed either on a box side or on the opposite side
- (£): Cap for identification of M5 pin pos. coil, to be removed during the TGC installation phase on the vehicle

- 1) Box
- 2) Top cover
- 3) Electrical BDS

Material and treatments:



View from A

DIMENSIONS AND TOLERANCES IN MILLIMETERS. DEFINED ACCORDING TO ISO 1101:2017.						
linear dimensions						
0,5 3	>3 6	>6 30	>30 120	>120 400	>400 1000	>1000 2000
±0,2	±0,3	±0,5	±0,8	±1,2	±2	±3
angle (for range of lengths)						
up to 10	>10 50	>50 120	>120 400	>120 400		
±1°30'	±1°	±0°30'	±0°15'			
●	FIT/ FUNCTION CRITICAL CHARACTERISTICS SYMBOL					
<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL					
CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE					
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS					
CP	DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE					
NAME		DATE				
DRAWN L. Dal Molin		24/05/2019				
CHECKED	-	-				
	-	-				
	-	-				
FORM NO. CVP-PE40-0013 REV A		 Littelfuse® Expertise Applied Answers Delivered				
FIRST ANGLE PROJECTION						
						
DO NOT SCALE DRAWING		SIZE: A2	DWG. NO.	OUTLINE	REV.	A
		SCALE 1:1		SHEET 1 OF 1		
		OL-08096600				