





DOVETAIL FEATURES
USED TO INTERLOCK
MULTIPLE HOLDERS



- NOTES:
- 1) BASE: UL94V-0 GLASS-FILLED PPA
M8 STUDS: SEE CHART
HEX NUTS & SPLIT WASHERS: SEE CHART
COVER: UL94V-0 ELASTOMER
 - 2) MAX FUSE RATING: 500A
 - 3) M8 STUD TORQUE: 12-18Nm
MOUNTING TORQUE (W/M6 BOLTS & WASHERS): 5Nm
 - 4) TEMPERATURE RATING: -40°C TO 125°C
 - 5) WIRE SIZE: 8mm² TO 30mm²



PART NO.	DESCRIPTION	MATERIAL (STUDS & HARDWARE)
02981028HXFCB	BASE ONLY (NO HARDWARE)	ZINC-PLATED STEEL
02981028HXFCC	COVER ONLY	-
02981028HXFC	ASSEMBLY	ZINC-PLATED STEEL
02981028HXFC-SS	ASSEMBLY	STAINLESS STEEL

COPIES TO			MTRL SPEC										SEE NOTES																																														
1	9	18	FINISH										N/A																																														
2	10	19																																																									
3	12	20																																																									
4	13	21	DRW K. HOOD										DATE 04/30/09										SCALE										1:2																										
5	14	23	CHK										DATE										SUPER DR																																				
6	15	33																																																									
7	16	43	APPD										DATE										FINSH GOOD WT										GRAMS/PIECE																										
8	17	53																																																									
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-mK)																																																											
DIMENSION										0.5 - 3										UP TO OVER 3 - 6										UP TO OVER 6 - 30										UP TO OVER 30 - 120										UP TO OVER 120 - 400									
TOLERANCE										±0.1										±0.1										±0.2										±0.3										±0.5									
3RD ANGLE PROJECTION																																																											
																																																											
TITLE																																																											
FLEX-MEGA FUSE HOLDER																																																											
															DES PLAINES, ILLINOIS 60016																																												
REVISION															DRWG. NO.																																												
D															OL-02981028HXFC																																												