

1.81	0.32
2.02	0.72
2.28	0.90
2.31	1.70
2.57	1.80
2.82	1.90
2.69	2.40
7.36	2.90
13.20	5.20
17.01	6.70
20.82	8.20
23.36	9.20
26.92	1.060
35.05	1.380
43.68	1.720
6.35	2.20
33.02	1.300

551806

$\frac{4.31}{4.57}$ DIA. 2 HOLES

REF.
20° TYP. →

BAT.-

OFF.

BAT $\frac{1}{2}$

6.04

7.36

6.92-

— .81 X 1.82 K'WAY

-BUSHING, 15/32-32UNS-2ATHD.
-HOUSING, ZINC DIE CAST

TERMINAL, STEEL

-SCREW-SEMS
8-32 X 6.35 LG., STEEL
-BAT #1 (6 REQ'D)

-BAT. #1

CIRCUIT #1
CIRCUIT #2

(6 REQ'D

- BAT #2

CIRCUIT #4

-CIRCUIT #3

NOTE:

Ⓜ ALL STEEL PARTS PLATED

2. HEX NUT & SCREWS TO BE

② BAGGED

DO NOT SCALE

DATE DRAWN
2-25-64

DATE BLUEPRINT

COLE-HERSEE COMPANY
BOSTON, MASS. 02127, U.S.A.

D.P.D.T. TOGGLE SW.

551806

METRIC

										DO NOT SCALE			
LET	WAS	DATE	BY	LET	WAS	DATE	BY	MATERIAL	DRAWN	CHECKED	APPROV'D.	SCALE	DATE DRAWN
								11	MF	LB		1:1	2-25-64
								FINISH	COLE-HERSEE COMPANY				DATE BLUEPRINT
								11	BOSTON, MASS. 02127, U.S.A.				
				N	ECN 01005	1/4/01	93	TOLERANCES					
				M	CHGR 214/25234	11/19/92	58	FRACTIONAL ±					
					REDRAWN	10.1.76	11	DECIMAL ± .75	D.P.D.T. TOGGLE SW.				551806