


REVISIONS					
REV.	DESCRIPTION	DATE	GCF / ECR	DESIGNED	APPROVED
A	First issue of outline drawing	01-Oct-21		L.Dal Molin	M.Tinto



ELECTRICAL DIAGRAM



CONTACT ARRANGEMENT

N. contacts	Function
T	85 Negative
31	86 Positive command
15	87 Exit
53M	30 Positive (+30)
53S	Not allocated

4		Male contact	Brass	5	EA
3		Box	Thermoplastic	1	EA
2		Self-adhesive label		1	EA
1		Top cover	Thermoplastic	1	EA
POS.	p/N	DESCRIPTION	MATERIAL	Q.TY	U/M




PRESCRIPTIONS

The top cover must have only the five male terminals of 6.35
therefore the terminal 2.8, designated with the letter I, must be cut.

Maximum admissible output load: 2 x 21 W

SAP drawing number: 10000115060

Material and treatments:

DIMENSIONS AND TOLERANCES IN MILLIMETERS, DEFINED ACCORDING TO ISO 1101-2017.						
linear dimensions						
0,5 3	>3 6	>6 30	>30 120	>120 400	>400 1000	>1000 2000
±0,2	±0,3	±0,5	±0,8	±1,2	±2	±3
angle (for range of lengths)						
up to 10		>10 50		>50 120		>120 400
±1°30'		±1°		±0°30'		±0°15'
	FIT/ FUNCTION CRITICAL CHARACTERISTICS SYMBOL					
<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL					
CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE					
	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS					
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE					
		NAME	DATE	 Littelfuse® Expertise Applied Answers Delivered		
DRAWN		L. Dal Molin	01-Oct-21			
CHECKED		-	-			
		-	-			
				TITLE		
FORM NO: CVP-PE40-0013 REV A		RELAY FOR REAR FOG LIGHTS				
FIRST ANGLE PROJECTION						
		SIZE: A3		DWG. NO. OL-05930700		OUTLINE REV. A
DO NOT SCALE DRAWING		SCALE 2:1				SHEET 1 OF 1