

$\varnothing 20.7 \pm 0.18$   
[ $\varnothing 0.813 \pm 0.007$ ]

$3.2 \pm 0.08$   
[ $0.125 \pm 0.003$ ]

$8.7 \pm 0.13$   
[ $0.343 \pm 0.005$ ]

$63.5 \pm 1.60$   
[ $2.500 \pm 0.063$ ]

$57.2 \pm 1.60$   
[ $2.250 \pm 0.063$ ]

$41.3 \pm 1.60$   
[ $1.625 \pm 0.063$ ]

$81.0 \pm 1.60$   
[ $3.189 \pm 0.063$ ]

$18.3 \pm 0.25$   
[ $0.720 \pm 0.010$ ]

# REVISION

REV	DATE	DESCRIPTION
A	6/27/23	526654GCP - RELEASE MRY

1				
NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M

## BILL OF MATERIAL

<S> CRITICAL CHARACTERISTIC FOR PART SAFETY/COMPLIANCE

● DENOTES CRITICAL CHARACTERISTICS.

CPK DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE

ST DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS.

CP DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.

A

MATL SPEC

FINISH

DRW  
JMoler


DATE  
6/20/2023

SCALE  
NTS

FINISH GOOD WT  
GRAMS/PIECE

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [ ] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994

3RD ANGLE  
PROJECTION



TITLE

L25S 35-60A OUTLINE

**Littelfuse**  
CHICAGO, ILLINOIS 60631

REVISION

A

DRWG NO.

OL-L25S060

SHEET 1 OF 1