

$\varnothing 63.50 \pm 0.38$   
[ $\varnothing 2.500 \pm 0.015$ ]

$9.53 \pm 0.15$   
[ $0.375 \pm 0.006$ ]

13.46  
[0.530]

33.27  
[1.310]

$103.20 \pm 1.59$   
[ $4.063 \pm 0.063$ ]

$142.83 \pm 1.59$   
[ $5.623 \pm 0.063$ ]


$173.05 \pm 1.59$   
[ $6.813 \pm 0.063$ ]

72.24  
[2.844]

$50.80 \pm 0.89$   
[ $2.000 \pm 0.035$ ]

# REVISION

REV	DATE	DESCRIPTION
A	7/18/23	526718GCP - RELEASE MRY

1					
NO	COMPONENT NO	DESCRIPTION		QTY/M	U/M
BILL OF MATERIAL					
<S>	CRITICAL CHARACTERISTIC FOR PART SAFETY/COMPLIANCE				
●	DENOTES CRITICAL CHARACTERISTICS.				
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE				
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS.				
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.				
MATL SPEC			FINISH		
DRW JMoler		DATE 6/26/2023	SCALE NTS	FINISH GOOD WT GRAMS/PIECE	
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [ ] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994					
3RD ANGLE PROJECTION					
TITLE L70QS 700-800A OUTLINE					
 <b>Littelfuse®</b> CHICAGO, ILLINOIS 60631			REVISION  A	DRWG NO.  OL-L70QS800	SHEET 1 OF 1