


2

1



Mechanical Dimensions :

A	B	C	D	E
0.063" $\pm$ 0.007" (1.6002 $\pm$ 0.1778mm)	0.0315" $\pm$ 0.007" (0.8001 to 0.1778 mm)	0.0394" Max (1.0007 mm Max)	0.0157" $\pm$ 0.010"(2X) (0.3987 $\pm$ 0.254mm (2X))	Solder Plated Terminations

Electrical Specifications :

Resistance (25 °C) Ω	Resistance Tolerance, $\pm\%$	Temp, Coefficient (%/°C)	Beta(K)	Temp Rating(°C)	Power Rating(V)	Packaging
100 to 100000	1 to 10	3.31 to 4.4	2000~5000	-55 ~ +150	40~400	Tape & Reel

A	Initial Release	RKM	04/04/2023	
Rev	Description	By	Date	ECO NO
Revision History				
Reference Legacy No.		USPxxxx REV x		

Project Code	XXXXXX			 Littelfuse®	
	Third Angle Projection				
Units	Inch(mm)			Division	IBU - Temperature Sensors
General Tolerances 0.X = ± 0.X 0.XX = ± 0.XX 0.XXX = ± 0.XXX				Title	End Banded NTC Thermistor Chips-0603
Drawn By	RKM			Finished Product Part Number	NSRB
				Internal No.	NSRB
Date	04/04/2023			Size	A
				Do Not Scale	Sheet 1 of 1

2

1