





Spare part cod 00226200
Protection open 70mmq



ELECTRICAL CHARACTERISTICS

- Nominal operating voltage: 12 + 24 V
- Max continuous current on contacts: 250 A at 23°C
- Max current short duration on contacts: 2000 A at 23°C for 30 sec.

MECHANICAL CHARACTERISTICS

- Number of electrical and mechanical operations: 50.000
- Locking torque nuts M10/M12: 20 Nm

PRESCRIPTIONS

- We suggest to fix the TGC to the structure by screws M8 UNI 5931:1984 and plane washers 8.4 x 17 UNI 6592:1969 under head
- (*): Data of production
- The distance between plunger bridge and fix contacts must be minimum 2 mm

SAP drawing number:

Material and treatments:

DIMENSIONS AND TOLERANCES IN MILLIMETERS, DEFINED ACCORDING TO ISO 1191:2017

linear dimensions

0,5	>3	≥6	>30	>120	>400	>1000
±0,2	±0,3	±0,5	±0,8	±1,2	±2	±3

angle (for range of lengths)

up to 10	≥10 50	120 120	≥120 400
±1°/30°	±1°	±0°/30°	±0°/15°

FUNCTION CRITICAL CHARACTERISTICS SYMBOL

SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL

CPK DENOTES CP CHARACTERISTICS MINIMUM CPK VALUE

DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE (PROCESSING PROCEDURE FOR MEASUREMENT) TRACKING TO BE DEFINED IN UTILITY/FUSE INSPECTION INSTRUCTIONS

CP DENOTES CP DIMENSIONS - MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

NAME	DATE
DRAWN: L. Dal Maso	27/05/2019
CHECKED:	

Expertise Applied Answers Delivered

TITLE

GENERAL ELECTRICAL MAIN SWITCH

IGC/RMCDE 24V

SIZE A1

SCALE 1:1

OUTPUT RATED

OL-08097460

SHEET 1 OF 1

A

FIRST ANGLE PROJECTION

DO NOT SCALE DRAWING