


## LSIC2SD120C10A 1200 V, 10 A SiC Schottky Barrier Diode





### Agency Approvals and Environmental

#### Environmental Approvals



### Pinout Diagram



### Product Summary

| Characteristic                     | Value | Unit |
|------------------------------------|-------|------|
| $V_{RRM}$                          | 1200  | V    |
| $I_F (T_C \leq 135^\circ\text{C})$ | 15    | A    |
| $Q_C (V_R: 0-800\text{ V})$        | 56    | nC   |

### Features

- AEC-Q101 Qualified
- MSL 1 Rated
- Positive temperature coefficient for safe operation and ease of paralleling
- 175 °C maximum operating junction temperature
- Excellent surge capability
- Extremely fast, temperature-independent switching behavior
- Dramatically reduced switching losses compared to Si bipolar diodes
- RoHS compliant, lead-free, and halogen-free

### Applications

- Boost diodes in PFC or DC/DC stages
- Switch-mode power supplies
- Solar inverters
- Uninterruptable power supplies
- Industrial motor drives
- Battery Chargers
- High speed rectifier

1. Maximum Ratings.....3

2. Thermal Characteristics .....3

3. Electrical Characteristics .....3

4. Performance Curves .....4

5.  $V_F$  Model for Simulation.....5

6. Package Dimensions.....6

7. Part Numbering and Marking.....6

8. Packing Options .....6

9. Packing Specifications.....7

## 1. Maximum Ratings

| Characteristic                               | Symbol        | Conditions                                                                  | Value      | Unit                 |
|----------------------------------------------|---------------|-----------------------------------------------------------------------------|------------|----------------------|
| Repetitive Peak Reverse Voltage              | $V_{RRM}$     | -                                                                           | 1200       | V                    |
| DC Blocking Voltage                          | $V_R$         | -                                                                           | 1200       | V                    |
| Continuous Forward Current                   | $I_F$         | $T_C = 25\text{ }^{\circ}\text{C}$                                          | 32         | A                    |
|                                              |               | $T_C = 135\text{ }^{\circ}\text{C}$                                         | 15         |                      |
|                                              |               | $T_C = 154\text{ }^{\circ}\text{C}$                                         | 10         |                      |
| Non-repetitive Forward Surge Current         | $I_{FSM}$     | $T_C = 25\text{ }^{\circ}\text{C}$ , $t_p = 10\text{ ms}$ , Half sine pulse | 80         | A                    |
| $I^2t$                                       | $\int I^2 dt$ | $T_C = 25\text{ }^{\circ}\text{C}$ , $t_p = 10\text{ ms}$ , Half sine pulse | 32         | $\text{A}^2\text{s}$ |
| Power Dissipation                            | $P_{Tot}$     | $T_C = 25\text{ }^{\circ}\text{C}$                                          | 150        | W                    |
|                                              |               | $T_C = 110\text{ }^{\circ}\text{C}$                                         | 65         |                      |
| Operating Junction Temperature               | $T_J$         | -                                                                           | -55 to 175 | $^{\circ}\text{C}$   |
| Storage Temperature                          | $T_{STG}$     | -                                                                           | -55 to 150 | $^{\circ}\text{C}$   |
| Lead Temperature for Soldering (MSL 1 Rated) | $T_{SOLD}$    | -                                                                           | 260        | $^{\circ}\text{C}$   |

## 2. Thermal Characteristics

| Characteristic                               | Symbol         | Value | Unit                 |
|----------------------------------------------|----------------|-------|----------------------|
| Maximum Thermal Resistance, junction-to-case | $R_{thJC,MAX}$ | 1.0   | $^{\circ}\text{C/W}$ |

## 3. Electrical Characteristics

| Characteristic            | Symbol | Conditions                                                  | Value |      |     | Unit          |
|---------------------------|--------|-------------------------------------------------------------|-------|------|-----|---------------|
|                           |        |                                                             | Min   | Typ  | Max |               |
| Forward Voltage           | $V_F$  | $I_F = 10\text{ A}$ , $T_J = 25\text{ }^{\circ}\text{C}$    | -     | 1.5  | 1.8 | V             |
|                           |        | $I_F = 10\text{ A}$ , $T_J = 175\text{ }^{\circ}\text{C}$   | -     | 2.0  | -   |               |
| Reverse Current           | $I_R$  | $V_R = 1200\text{ V}$ , $T_J = 25\text{ }^{\circ}\text{C}$  | -     | <1   | 100 | $\mu\text{A}$ |
|                           |        | $V_R = 1200\text{ V}$ , $T_J = 175\text{ }^{\circ}\text{C}$ | -     | 4    | -   |               |
| Total Capacitance         | C      | $V_R = 1\text{ V}$ , $f = 1\text{ MHz}$                     | -     | 580  | -   | pF            |
|                           |        | $V_R = 400\text{ V}$ , $f = 1\text{ MHz}$                   | -     | 53   | -   |               |
|                           |        | $V_R = 800\text{ V}$ , $f = 1\text{ MHz}$                   | -     | 40   | -   |               |
| Total Capacitive Charge   | $Q_C$  | $V_R = 800\text{ V}$ , $Q_C = \int C(V) dV$                 | -     | 56   | -   | nC            |
| Capacitance Stored Energy | $E_C$  | $V_R = 800\text{ V}$                                        | -     | 12.8 | -   | $\mu\text{J}$ |

## 4. Performance Curves

Figure 1. Typical Forward Characteristics




Figure 2. Typical Reverse Characteristics




Figure 3. Power Derating




Figure 4. Current Derating




Figure 5. Capacitance vs. Reverse Voltage




Figure 6. Capacitive Charge vs. Reverse Voltage




Figure 7. Stored Energy vs. Reverse Voltage






Figure 8. Transient Thermal Impedance



## 5. V<sub>F</sub> Model for Simulation



$$V_F(T_J) = V_0 + IR_0$$


$$V_0 = -1.11 \times 10^{-3} \cdot T_J + 1.01 \times 10^0$$

$$R_0 = 1.61 \times 10^{-6} \cdot T_J^2 + 1.50 \times 10^{-4} \cdot T_J + 4.35 \times 10^{-2}$$

Notes:


- T<sub>J</sub> is junction temperature in °C
- Range valid from 25 °C to 175 °C
- Model represents performance of a typical part

## 6. Package Dimensions




| Symbol | Millimeters |        |
|--------|-------------|--------|
|        | Min         | Max    |
| A      | 2.159       | 2.413  |
| A1     | -           | 0.127  |
| b      | 0.635       | 1.067  |
| b3     | 4.953       | 5.461  |
| c      | 0.457       | 0.610  |
| c2     | -           | 0.889  |
| (c2)   | 0.457       | 0.610  |
| D      | 5.969       | 6.223  |
| D1     | 5.207       | 5.715  |
| E      | 6.350       | 6.731  |
| E1     | 4.318       | 5.207  |
| e      | 2.29 REF.   |        |
| H      | 9.398       | 10.414 |
| L      | 1.016       | 1.778  |
| L2     | 0.25 REF.   |        |
| L3     | 0.889       | 1.270  |
| L4     | 0.000       | 0.152  |
| M      | 15°         |        |
| P      | -           | 5°     |

Recommended Solder Pad Layout



UNIT: Inch [mm]

## 7. Part Numbering and Marking




SiC = SiC  
 2 = Gen 2  
 SD = Schottky Barrier Diode  
 120 = Voltage Rating (1200 V)  
 C = Package (TO-252-2L)  
 10 = Current Rating (10 A)  
 A = AEC-Q101 qualified  
 YY = Year  
 WW = Week  
 D = Special Code  
 ZZZZZZ-ZZ = Lot Number

## 8. Packing Options

| Part Number    | Marking       | Packing Mode | M.O.Q. |
|----------------|---------------|--------------|--------|
| LSIC2SD120C10A | SIC2SD120C10A | Tape & Reel  | 2500   |

## 9. Packing Specifications


### TO-252 Carrier Tape & Reel Specifications



1. Material: Black Conductive Polystyrene
2. 10 sprocket hole pitch cumulative tolerance  $\pm 0.20$
3. Camber not to exceed 1 mm in 100 mm.
4. Pocket position relative to sprocket hole measured as true position of pocket, not pocket hole.
5. Device orientation: TRL (leads perpendicular to the sprocket)
6. General tolerance is  $\pm 0.10$  mm unless otherwise specified.

#### COVER TAPE SPECS:

|                  |                                               |
|------------------|-----------------------------------------------|
| Width            | : 13.5 mm                                     |
| Base Material    | : less than $1.2 \times 10^{-10}$ ohms/square |
|                  | : Transparent polyester, static dissipative   |
| Adhesive Layer   | : Polyethylene                                |
| Total Thickness  | : 60 Micron                                   |
| Tensile Strength | : 4-6 kg/mm <sup>2</sup>                      |
| Elongation       | : 91%                                         |
| Tearing Strength | : 11 kg/mm <sup>2</sup>                       |
| Shelf life       | : 2 years                                     |



For additional information please visit [www.Littelfuse.com/powersemi](http://www.Littelfuse.com/powersemi)

**Disclaimer Notice** - Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly forth in applicable Littelfuse product documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation.

Read complete Disclaimer Notice at [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics)