


# HiPerFET™ Power MOSFETs

N-Channel Enhancement Mode  
High dv/dt, Low  $t_{rr}$ , HDMOS™ Family

Obsolete:  
IXFM35N30

~~IXFH/IXFM35N30~~  
IXFH40N30  
IXFM40N30




| $V_{DSS}$ | $I_{D25}$ | $R_{DS(on)}$ |
|-----------|-----------|--------------|
| 300 V     | 35 A      | 100 mΩ       |
| 300 V     | 40 A      | 85 mΩ        |
| 300 V     | 40 A      | 88 mΩ        |

$t_{rr} \leq 200$  ns

| Symbol    | Test Conditions                                                                                                  | Maximum Ratings             |              |
|-----------|------------------------------------------------------------------------------------------------------------------|-----------------------------|--------------|
| $V_{DSS}$ | $T_J = 25^\circ\text{C}$ to $150^\circ\text{C}$                                                                  | 300                         | V            |
| $V_{DGR}$ | $T_J = 25^\circ\text{C}$ to $150^\circ\text{C}$ ; $R_{GS} = 1$ MΩ                                                | 300                         | V            |
| $V_{GS}$  | Continuous                                                                                                       | $\pm 20$                    | V            |
| $V_{GSM}$ | Transient                                                                                                        | $\pm 30$                    | V            |
| $I_{D25}$ | $T_C = 25^\circ\text{C}$                                                                                         | 35N30<br>40N30              | 35<br>40 A   |
| $I_{DM}$  | $T_C = 25^\circ\text{C}$ , pulse width limited by $T_{JM}$                                                       | 35N30<br>40N30              | 140<br>160 A |
| $I_{AR}$  | $T_C = 25^\circ\text{C}$                                                                                         | 35N30<br>40N30              | 35<br>40 A   |
| $E_{AR}$  | $T_C = 25^\circ\text{C}$                                                                                         | 30                          | mJ           |
| dv/dt     | $I_S \leq I_{DM}$ , $di/dt \leq 100$ A/μs, $V_{DD} \leq V_{DSS}$ ,<br>$T_J \leq 150^\circ\text{C}$ , $R_G = 2$ Ω | 5                           | V/ns         |
| $P_D$     | $T_C = 25^\circ\text{C}$                                                                                         | 300                         | W            |
| $T_J$     |                                                                                                                  | -55 ... +150                | °C           |
| $T_{JM}$  |                                                                                                                  | 150                         | °C           |
| $T_{stg}$ |                                                                                                                  | -55 ... +150                | °C           |
| $T_L$     | 1.6 mm (0.062 in.) from case for 10 s                                                                            | 300                         | °C           |
| $M_d$     | Mounting torque                                                                                                  | 1.13/10                     | Nm/lb.in.    |
| Weight    |                                                                                                                  | TO-204 = 18 g, TO-247 = 6 g |              |


| Symbol       | Test Conditions                                                                                        | Characteristic Values<br>( $T_J = 25^\circ\text{C}$ , unless otherwise specified) |      |                               |
|--------------|--------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|------|-------------------------------|
|              |                                                                                                        | min.                                                                              | typ. | max.                          |
| $V_{DSS}$    | $V_{GS} = 0$ V, $I_D = 250$ μA                                                                         | 300                                                                               |      | V                             |
| $V_{GS(th)}$ | $V_{DS} = V_{GS}$ , $I_D = 4$ mA                                                                       | 2                                                                                 |      | 4 V                           |
| $I_{GSS}$    | $V_{GS} = \pm 20$ V <sub>DC</sub> , $V_{DS} = 0$                                                       |                                                                                   |      | $\pm 100$ nA                  |
| $I_{DSS}$    | $V_{DS} = 0.8 \cdot V_{DSS}$ , $V_{GS} = 0$ V<br>$T_J = 25^\circ\text{C}$<br>$T_J = 125^\circ\text{C}$ |                                                                                   |      | 200 μA<br>1 mA                |
| $R_{DS(on)}$ | $V_{GS} = 10$ V, $I_D = 0.5 I_{D25}$<br>Pulse test, $t \leq 300$ μs, duty cycle $d \leq 2$ %           | 35N30<br>FH40N30<br>FM40N30                                                       |      | 0.100 Ω<br>0.085 Ω<br>0.088 Ω |

TO-247 AD (IXFH)



TO-204 AE (IXFM)

Package  
unavailable



G = Gate,  
S = Source,

D = Drain,  
TAB = Drain

## Features

- International standard packages
- Low  $R_{DS(on)}$  HDMOS™ process
- Rugged polysilicon gate cell structure
- Unclamped Inductive Switching (UIS) rated
- Low package inductance
  - easy to drive and to protect
- Fast intrinsic Rectifier

## Applications

- DC-DC converters
- Synchronous rectification
- Battery chargers
- Switched-mode and resonant-mode power supplies
- AC choppers
- AC motor control
- Temperature and lighting controls
- Low voltage relays


## Advantages

- Easy to mount with 1 screw (TO-247) (isolated mounting screw hole)
- Space savings
- High power density


| Symbol       | Test Conditions                                                                                             | Characteristic Values<br>( $T_J = 25^\circ\text{C}$ , unless otherwise specified) |      |      |
|--------------|-------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|------|------|
|              |                                                                                                             | min.                                                                              | typ. | max. |
| $g_{fs}$     | $V_{DS} = 10\text{ V}$ ; $I_D = 0.5 I_{D25}$ , pulse test                                                   | 22                                                                                | 25   | S    |
| $C_{iss}$    | $V_{GS} = 0\text{ V}$ , $V_{DS} = 25\text{ V}$ , $f = 1\text{ MHz}$                                         | 4800                                                                              | 745  | pF   |
| $C_{oss}$    |                                                                                                             |                                                                                   |      | pF   |
| $C_{rss}$    |                                                                                                             |                                                                                   |      | pF   |
| $t_{d(on)}$  | $V_{GS} = 10\text{ V}$ , $V_{DS} = 0.5 \cdot V_{DSS}$ , $I_D = 0.5 I_{D25}$<br>$R_G = 2\ \Omega$ (External) | 20                                                                                | 30   | ns   |
| $t_r$        |                                                                                                             | 60                                                                                | 90   | ns   |
| $t_{d(off)}$ |                                                                                                             | 75                                                                                | 100  | ns   |
| $t_f$        |                                                                                                             | 45                                                                                | 90   | ns   |
| $Q_{g(on)}$  | $V_{GS} = 10\text{ V}$ , $V_{DS} = 0.5 \cdot V_{DSS}$ , $I_D = 0.5 I_{D25}$                                 | 177                                                                               | 200  | nC   |
| $Q_{gs}$     |                                                                                                             | 28                                                                                | 50   | nC   |
| $Q_{gd}$     |                                                                                                             | 78                                                                                | 105  | nC   |
| $R_{thJC}$   |                                                                                                             | 0.25                                                                              | 0.42 | K/W  |
| $R_{thCK}$   |                                                                                                             |                                                                                   |      | K/W  |

**Source-Drain Diode**







| Symbol   | Test Conditions                                                                                          | Characteristic Values<br>( $T_J = 25^\circ\text{C}$ , unless otherwise specified) |      |                  |
|----------|----------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|------|------------------|
|          |                                                                                                          | min.                                                                              | typ. | max.             |
| $I_S$    | $V_{GS} = 0\text{ V}$                                                                                    | 35N30<br>40N30                                                                    |      | 35 A<br>40 A     |
| $I_{SM}$ | Repetitive;<br>pulse width limited by $T_{JM}$                                                           | 35N30<br>40N30                                                                    |      | 140 A<br>160 A   |
| $V_{SD}$ | $I_F = I_S$ , $V_{GS} = 0\text{ V}$ ,<br>Pulse test, $t \leq 300\ \mu\text{s}$ , duty cycle $d \leq 2\%$ |                                                                                   |      | 1.5 V            |
| $t_{rr}$ | $I_F = I_S$ , $-di/dt = 100\text{ A}/\mu\text{s}$ ,<br>$V_R = 100\text{ V}$                              | $T_J = 25^\circ\text{C}$<br>$T_J = 125^\circ\text{C}$                             |      | 200 ns<br>350 ns |






**TO-247 AD (IXFH) Outline**


| Dim. | Millimeter<br>Min. Max. | Inches<br>Min. Max. |
|------|-------------------------|---------------------|
| A    | 19.81 20.32             | 0.780 0.800         |
| B    | 20.80 21.46             | 0.819 0.845         |
| C    | 15.75 16.26             | 0.610 0.640         |
| D    | 3.55 3.65               | 0.140 0.144         |
| E    | 4.32 5.49               | 0.170 0.216         |
| F    | 5.4 6.2                 | 0.212 0.244         |
| G    | 1.65 2.13               | 0.065 0.084         |
| H    | - 4.5                   | - 0.177             |
| J    | 1.0 1.4                 | 0.040 0.055         |
| K    | 10.8 11.0               | 0.426 0.433         |
| L    | 4.7 5.3                 | 0.185 0.209         |
| M    | 0.4 0.8                 | 0.016 0.031         |
| N    | 1.5 2.49                | 0.087 0.102         |

**TO-204 AE (IXFM) Outline**


| Dim. | Millimeter<br>Min. Max. | Inches<br>Min. Max. |
|------|-------------------------|---------------------|
| A    | 38.61 39.12             | 1.520 1.540         |
| B    | - 22.22                 | - 0.875             |
| C    | 6.40 11.40              | 0.252 0.449         |
| D    | 1.45 1.60               | 0.057 0.063         |
| E    | 1.52 3.43               | 0.060 0.135         |
| F    | 30.15 BSC               | 1.187 BSC           |
| G    | 10.67 11.17             | 0.420 0.440         |
| H    | 5.21 5.71               | 0.205 0.225         |
| J    | 16.64 17.14             | 0.655 0.675         |
| K    | 11.18 12.19             | 0.440 0.480         |
| Q    | 3.84 4.19               | 0.151 0.165         |
| R    | 25.16 26.66             | 0.991 1.050         |

**Fig.1. Output Characteristics**

**Fig. 2. Input Admittance**

**Fig. 3. Rds(on) vs. Drain Current**

**Fig. 4. Temperature Dependence of Drain to Source Resistance**

**Fig. 5. Drain Current vs. Case Temperature**

**Fig. 6. Temperature Dependence of Breakdown Voltage and Threshold Voltage**


**Fig.7 Gate Charge Characteristic Curve**

**Fig.8 Forward Bias Safe Operating Area**

**Fig.9 Capacitance Curves**

**Fig.10 Source Current vs. Source**

**Fig.11 Transient Thermal Impedance**




---

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics).