



CoolMOS™ 1) Power MOSFET with HiPerDyn™ FRED Buck and Boost Topologies

Electrically isolated back surface
2500 V electrical isolation
N-Channel Enhancement Mode
Low $R_{DS(on)}$, high V_{DSS} MOSFET
Ultra low gate charge



$$\begin{aligned} I_{D25} &= 15 \text{ A} \\ V_{DSS} &= 600 \text{ V} \\ R_{DS(on) \text{ max}} &= 0.165 \Omega \end{aligned}$$

ISOPLUS i4™



MOSFET T			
Symbol	Conditions	Maximum Ratings	
V_{DSS}	$T_{VJ} = 25^\circ\text{C}$	600	V
V_{GS}		± 20	V
I_{D25}	$T_C = 25^\circ\text{C}$	15	A
I_{D90}	$T_C = 90^\circ\text{C}$	11	A
E_{AS}	single pulse repetitive } $I_D = 7.9 \text{ A}; T_C = 25^\circ\text{C}$	522	mJ
E_{AR}		0.79	mJ
dV/dt	MOSFET dV/dt ruggedness $V_{DS} = 0 \dots 480 \text{ V}$	50	V/ns

Symbol	Conditions	Characteristic Values			
		(T _{VJ} = 25°C, unless otherwise specified)			
		min.	typ.	max.	
$R_{DS(on)}$	$V_{GS} = 10 \text{ V}; I_D = 12 \text{ A}$		150	165	mΩ
$V_{GS(th)}$	$V_{DS} = V_{GS}; I_D = 0.79 \text{ mA}$	2.5	3	3.5	V
I_{DSS}	$V_{DS} = 600 \text{ V}; V_{GS} = 0 \text{ V}$ $T_{VJ} = 25^\circ\text{C}$ $T_{VJ} = 125^\circ\text{C}$		10	1	μA μA
I_{GSS}	$V_{GS} = \pm 20 \text{ V}; V_{DS} = 0 \text{ V}$			100	nA
C_{iss}	$V_{GS} = 0 \text{ V}; V_{DS} = 100 \text{ V}$ $f = 1 \text{ MHz}$		2000		pF
C_{oss}			100		pF
Q_g	$V_{GS} = 0 \text{ to } 10 \text{ V}; V_{DS} = 400 \text{ V}; I_D = 12 \text{ A}$		40	52	nC
Q_{gs}			9		nC
Q_{gd}			13		nC
$t_{d(on)}$	$V_{GS} = 10 \text{ V}; V_{DS} = 400 \text{ V}$ $I_D = 12 \text{ A}; R_G = 3.3 \Omega$		12		ns
t_r			5		ns
$t_{d(off)}$			50		ns
t_f			5		ns
E_{on}			tbd		mJ
E_{off}			tbd		mJ
$E_{rec off}$			tbd		mJ
R_{thJC}	with heat transfer paste			1.1	K/W
R_{thCH}			0.35		K/W

Features

- Silicon chip on Direct-Copper-Bond substrate
 - high power dissipation
 - isolated mounting surface
 - 2500 V electrical isolation
 - low drain to tab capacitance (< 40 pF)
- Fast CoolMOS™ 1) power MOSFET 4th generation
 - high blocking capability
 - lowest resistance
 - avalanche rated for unclamped inductive switching (UIS)
 - low thermal resistance due to reduced chip thickness
- Enhanced total power density
- HiPerDyn™ FRED
 - consisting of series connected diodes
 - enhanced dynamic behaviour for high frequency operation

Applications

- Switched mode power supplies (SMPS)
- Uninterruptible power supplies (UPS)
- Power factor correction (PFC)

Advantages

- Easy assembly: no screws or isolation foils required
- Space savings
- High power density
- High reliability

1) CoolMOS™ is a trademark of Infineon Technologies AG.

MOSFET T Source-Drain Diode


Symbol	Conditions	Characteristic Values			
		(T _{VJ} = 25°C, unless otherwise specified)			
		min.	typ.	max.	
I _S	V _{GS} = 0 V			12	A
V _{SD}	I _F = 12 A; V _{GS} = 0 V		0.9	1.2	V
t _{rr}	I _F = 12 A; -di _F /dt = 100 A/μs; V _R = 400 V		390		ns
Q _{RM}			7.5		μC
I _{RM}			38		A

Diode D (data for series connection)

Symbol	Conditions	Maximum Ratings			
V _{RRM}	T _{VJ} = 25°C to 150°C			600	V
I _{F25}	T _C = 25°C			15	A
I _{F90}	T _C = 90°C			8	A
Symbol	Conditions	Characteristic Values			
		min.	typ.	max.	
V _F	I _F = 15 A	T _{VJ} = 25°C		2.50	V
	I _F = 30 A			3.00	V
	I _F = 15 A	T _{VJ} = 150°C		2.00	A
	I _F = 30 A			2.55	A
I _R	V _R = V _{RRM}	T _{VJ} = 25°C		1	μA
		T _{VJ} = 150°C		0.08	mA
I _{FSM}	t = 10 ms (50 Hz), sine;	T _{VJ} = 45°C		150	A
I _{RM}	I _F = 20 A; V _R = 100 V; -di _F /dt = 200 A/μs	T _{VJ} = 25°C		3	A
t _{rr}				35	ns
R _{thJC}	with heat transfer paste			2.4	K/W
R _{thJH}			0.8		K/W

Component

Symbol	Conditions	Maximum Ratings			
T _{VJ}	operating			-55...+150	°C
T _{stg}	storage			-55...+125	°C
V _{ISOL}	I _{ISOL} < 1 mA; 50/60 Hz			2500	V~
F _C	mounting force with clip			20...120	N
Symbol	Conditions	Characteristic Values			
		min.	typ.	max.	
C _P	coupling capacity between shorted pins and mounting tab in the case		40		pF
d _S , d _A	pin - pin	1.7			mm
d _S , d _A	pin - backside metal	5.5			mm
Weight			9		g

ISOPLUS i4™ Outline




Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.