


# MegaMOS™FET

IXTH 35N30  
IXTH 40N30  
IXTM 40N30

| $V_{DSS}$ | $I_{D25}$ | $R_{DS(on)}$   |
|-----------|-----------|----------------|
| 300 V     | 35 A      | 0.10 $\Omega$  |
| 300 V     | 40 A      | 0.085 $\Omega$ |
| 300 V     | 40 A      | 0.088 $\Omega$ |


## N-Channel Enhancement Mode



| Symbol                                                                          | Test Conditions                                                               | Maximum Ratings             |                  |
|---------------------------------------------------------------------------------|-------------------------------------------------------------------------------|-----------------------------|------------------|
| $V_{DSS}$                                                                       | $T_J = 25^\circ\text{C}$ to $150^\circ\text{C}$                               | 300                         | V                |
| $V_{DGR}$                                                                       | $T_J = 25^\circ\text{C}$ to $150^\circ\text{C}$ ; $R_{GS} = 1\text{ M}\Omega$ | 300                         | V                |
| $V_{GS}$                                                                        | Continuous                                                                    | $\pm 20$                    | V                |
| $V_{GSM}$                                                                       | Transient                                                                     | $\pm 30$                    | V                |
| $I_{D25}$                                                                       | $T_C = 25^\circ\text{C}$                                                      | 35N30 35<br>40N30 40        | A                |
| $I_{DM}$                                                                        | $T_C = 25^\circ\text{C}$ , pulse width limited by $T_{JM}$                    | 35N30 140<br>40N30 160      | A                |
| $P_D$                                                                           | $T_C = 25^\circ\text{C}$                                                      | 300                         | W                |
| $T_J$                                                                           |                                                                               | -55 ... +150                | $^\circ\text{C}$ |
| $T_{JM}$                                                                        |                                                                               | 150                         | $^\circ\text{C}$ |
| $T_{stg}$                                                                       |                                                                               | -55 ... +150                | $^\circ\text{C}$ |
| $M_d$                                                                           | Mounting torque                                                               | 1.13/10                     | Nm/lb.in.        |
| Weight                                                                          |                                                                               | TO-204 = 18 g, TO-247 = 6 g |                  |
| Maximum lead temperature for soldering<br>1.6 mm (0.062 in.) from case for 10 s |                                                                               | 300                         | $^\circ\text{C}$ |

TO-247 AD (IXTH)

TO-204 AE (IXTM)



G = Gate,  
S = Source,

D = Drain,  
TAB = Drain

### Features

- International standard packages
- Low  $R_{DS(on)}$  HDMOS™ process
- Rugged polysilicon gate cell structure
- Low package inductance (< 5 nH)
  - easy to drive and to protect
- Fast switching times

### Applications

- Switch-mode and resonant-mode power supplies
- Motor controls
- Uninterruptible Power Supplies (UPS)
- DC choppers

### Advantages

- Easy to mount with 1 screw (TO-247) (isolated mounting screw hole)
- Space savings
- High power density


| Symbol                                                                | Test Conditions                                        | Characteristic Values<br>( $T_J = 25^\circ\text{C}$ , unless otherwise specified) |      |                                                   |
|-----------------------------------------------------------------------|--------------------------------------------------------|-----------------------------------------------------------------------------------|------|---------------------------------------------------|
|                                                                       |                                                        | min.                                                                              | typ. | max.                                              |
| $V_{DSS}$                                                             | $V_{GS} = 0\text{ V}$ , $I_D = 250\text{ }\mu\text{A}$ | 300                                                                               |      | V                                                 |
| $V_{GS(th)}$                                                          | $V_{DS} = V_{GS}$ , $I_D = 250\text{ }\mu\text{A}$     | 2                                                                                 |      | V                                                 |
| $I_{GSS}$                                                             | $V_{GS} = \pm 20\text{ V}$ , $V_{DS} = 0$              |                                                                                   |      | $\pm 100\text{ nA}$                               |
| $I_{DSS}$                                                             | $V_{DS} = 0.8 \cdot V_{DSS}$ , $V_{GS} = 0\text{ V}$   |                                                                                   |      | 200 $\mu\text{A}$<br>1 mA                         |
| $R_{DS(on)}$                                                          | $V_{GS} = 10\text{ V}$ , $I_D = 0.5 I_{D25}$           |                                                                                   |      | 0.10 $\Omega$<br>0.085 $\Omega$<br>0.088 $\Omega$ |
| Pulse test, $t \leq 300\text{ }\mu\text{s}$ , duty cycle $d \leq 2\%$ |                                                        |                                                                                   |      |                                                   |

| Symbol       | Test Conditions                                                                                         | Characteristic Values<br>( $T_J = 25^\circ\text{C}$ , unless otherwise specified) |      |          |
|--------------|---------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|------|----------|
|              |                                                                                                         | min.                                                                              | typ. | max.     |
| $g_{fs}$     | $V_{DS} = 10\text{ V}; I_D = 0.5 \cdot I_{D25}$ , pulse test                                            | 22                                                                                | 25   | S        |
| $C_{iss}$    | $V_{GS} = 0\text{ V}, V_{DS} = 25\text{ V}, f = 1\text{ MHz}$                                           |                                                                                   | 4600 | pF       |
| $C_{oss}$    |                                                                                                         |                                                                                   | 650  | pF       |
| $C_{rss}$    |                                                                                                         |                                                                                   | 240  | pF       |
| $t_{d(on)}$  | $V_{GS} = 10\text{ V}, V_{DS} = 0.5 \cdot V_{DSS}, I_D = 0.5 I_{D25}$<br>$R_G = 2\ \Omega$ , (External) |                                                                                   | 24   | 30 ns    |
| $t_r$        |                                                                                                         |                                                                                   | 40   | 90 ns    |
| $t_{d(off)}$ |                                                                                                         |                                                                                   | 75   | 100 ns   |
| $t_f$        |                                                                                                         |                                                                                   | 40   | 90 ns    |
| $Q_{g(on)}$  | $V_{GS} = 10\text{ V}, V_{DS} = 0.5 \cdot V_{DSS}, I_D = 0.5 I_{D25}$                                   |                                                                                   | 190  | 220 nC   |
| $Q_{gs}$     |                                                                                                         |                                                                                   | 28   | 50 nC    |
| $Q_{gd}$     |                                                                                                         |                                                                                   | 85   | 105 nC   |
| $R_{thJC}$   |                                                                                                         |                                                                                   | 0.25 | 0.42 K/W |
| $R_{thCK}$   |                                                                                                         |                                                                                   |      | K/W      |

### Source-Drain Diode

| Symbol   | Test Conditions                                                                                       | Characteristic Values<br>( $T_J = 25^\circ\text{C}$ , unless otherwise specified) |      |                |
|----------|-------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|------|----------------|
|          |                                                                                                       | min.                                                                              | typ. | max.           |
| $I_S$    | $V_{GS} = 0\text{ V}$                                                                                 | 35N30<br>40N30                                                                    |      | 35 A<br>40 A   |
| $I_{SM}$ | Repetitive;<br>pulse width limited by $T_{JM}$                                                        | 35N30<br>40N30                                                                    |      | 140 A<br>160 A |
| $V_{SD}$ | $I_F = I_S, V_{GS} = 0\text{ V}$ ,<br>Pulse test, $t \leq 300\ \mu\text{s}$ , duty cycle $d \leq 2\%$ |                                                                                   |      | 1.5 V          |
| $t_{rr}$ | $I_F = I_S, -di/dt = 100\text{ A}/\mu\text{s}, V_R = 100\text{ V}$                                    |                                                                                   | 400  | ns             |


### TO-247 AD (IXTH) Outline



Terminals: 1 - Gate 2 - Drain  
3 - Source Tab - Drain

| Dim.           | Millimeter<br>Min. Max. | Inches<br>Min. Max. |
|----------------|-------------------------|---------------------|
| A              | 4.7 5.3                 | .185 .209           |
| A <sub>1</sub> | 2.2 2.54                | .087 .102           |
| A <sub>2</sub> | 2.2 2.6                 | .059 .098           |
| b              | 1.0 1.4                 | .040 .055           |
| b <sub>1</sub> | 1.65 2.13               | .065 .084           |
| b <sub>2</sub> | 2.87 3.12               | .113 .123           |
| C              | .4 .8                   | .016 .031           |
| D              | 20.80 21.46             | .819 .845           |
| E              | 15.75 16.26             | .610 .640           |
| e              | 5.20 5.72               | 0.205 0.225         |
| L              | 19.81 20.32             | .780 .800           |
| L1             | 4.50                    | .177                |
| ØP             | 3.55 3.65               | .140 .144           |
| Q              | 5.89 6.40               | 0.232 0.252         |
| R              | 4.32 5.49               | .170 .216           |
| S              | 6.15 BSC                | .242 BSC            |

### TO-204AE (IXTM) Outline



Pins 1 - Gate 2 - Source  
Case - Drain

| Dim.            | Millimeter<br>Min. Max. | Inches<br>Min. Max. |
|-----------------|-------------------------|---------------------|
| A               | 6.4 11.4                | .250 .450           |
| A <sub>1</sub>  | 1.53 3.42               | .060 .135           |
| Øb              | 1.45 1.60               | .057 .063           |
| ØD              | 22.22                   | .875                |
| e               | 10.67 11.17             | .420 .440           |
| e <sub>1</sub>  | 5.21 5.71               | .205 .225           |
| L               | 11.18 12.19             | .440 .480           |
| Øp              | 3.84 4.19               | .151 .165           |
| Øp <sub>1</sub> | 3.84 4.19               | .151 .165           |
| q               | 30.15 BSC               | 1.187 BSC           |
| R               | 12.58 13.33             | .495 .525           |
| R <sub>1</sub>  | 3.33 4.77               | .131 .188           |
| s               | 16.64 17.14             | .655 .675           |

Fig. 1 Output Characteristics




Fig. 2 Input Admittance




Fig. 3  $R_{DS(on)}$  vs. Drain Current


Fig. 4 Temperature Dependence of Drain to Source Resistance




Fig. 5 Drain Current vs. Case Temperature




Fig. 6 Temperature Dependence of Breakdown and Threshold Voltage




Fig.7 Gate Charge Characteristic Curve




Fig.8 Forward Bias Safe Operating Area




Fig.9 Capacitance Curves




Fig.10 Source Current vs. Source to Drain Voltage





Fig.11 Transient Thermal Impedance





---

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics).