


High Voltage, High Gain BiMOSFET™ Monolithic Bipolar MOS Transistor

IXBA12N300HV IXBT12N300HV


$$V_{CES} = 3000V$$

$$I_{C110} = 12A$$


$$V_{CE(sat)} \leq 3.2V$$



TO-263HV
(IXBA..HV)



TO-268HV
(IXBT..HV)



G = Gate
E = Emitter

C = Collector
Tab = Collector

Symbol	Test Conditions	Maximum Ratings	
V_{CES}	$T_J = 25^\circ C$ to $150^\circ C$	3000	V
V_{CGR}	$T_J = 25^\circ C$ to $150^\circ C$, $R_{GE} = 1M\Omega$	3000	V
V_{GES}	Continuous	± 20	V
V_{GEM}	Transient	± 30	V
I_{C25}	$T_C = 25^\circ C$	30	A
I_{C110}	$T_C = 110^\circ C$	12	A
I_{CM}	$T_C = 25^\circ C$, 1ms	100	A
SSOA (RBSOA)	$V_{GE} = 15V$, $T_{VJ} = 125^\circ C$, $R_G = 30\Omega$ Clamped Inductive Load	$I_{CM} = 98$ 1500	A V
P_c	$T_C = 25^\circ C$	160	W
T_J		-55 ... +150	$^\circ C$
T_{JM}		150	$^\circ C$
T_{stg}		-55 ... +150	$^\circ C$
T_{SOLD}	Plastic Body for 10s	260	$^\circ C$
Weight	TO-263HV	2.5	g
	TO-268HV	4.0	g

Features

- High Voltage Package
- High Blocking Voltage
- Anti-Parallel Diode
- Low Conduction Losses

Advantages

- Low Gate Drive Requirement
- High Power Density

Applications:

- Switch-Mode and Resonant-Mode Power Supplies
- Uninterruptible Power Supplies (UPS)
- Laser Generators
- Capacitor Discharge Circuits
- AC Switches

Symbol	Test Conditions ($T_J = 25^\circ C$ Unless Otherwise Specified)	Characteristic Values		
		Min.	Typ.	Max.
BV_{CES}	$I_C = 250\mu A$, $V_{GE} = 0V$	3000		V
$V_{GE(th)}$	$I_C = 250\mu A$, $V_{CE} = V_{GE}$	3.0		5.0 V
I_{CES}	$V_{CE} = 0.8 \cdot V_{CES}$, $V_{GE} = 0V$ $T_J = 125^\circ C$			25 μA 1 mA
I_{GES}	$V_{CE} = 0V$, $V_{GE} = \pm 20V$			± 100 nA
$V_{CE(sat)}$	$I_C = 12A$, $V_{GE} = 15V$, Note 1 $T_J = 125^\circ C$	2.8	3.2	V
		3.5		V

Symbol Test Conditions

(T_J = 25°C Unless Otherwise Specified)

Characteristic Values

		Min.	Typ.	Max.
g_{fs}	I _C = 12A, V _{CE} = 10V, Note 1	6.5	10.8	S
C_{ies}	V _{CE} = 25V, V _{GE} = 0V, f = 1MHz		1290	pF
C_{oes}			56	pF
C_{res}			19	pF
Q_{g(on)}	I _C = 12A, V _{GE} = 15V, V _{CE} = 1000V		62	nC
Q_{ge}			13	nC
Q_{gc}			8.5	nC
t_{d(on)}	Resistive Switching Times, T_J = 25°C I _C = 12A, V _{GE} = 15V V _{CE} = 1250V, R _G = 10Ω		64	ns
t_r			140	ns
t_{d(off)}			180	ns
t_f			540	ns
t_{d(on)}	Resistive Switching Times, T_J = 125°C I _C = 12A, V _{GE} = 15V V _{CE} = 1250V, R _G = 10Ω		65	ns
t_r			395	ns
t_{d(off)}			175	ns
t_f			530	ns
R_{thJC}			0.78	°C/W

Reverse Diode

Symbol Test Conditions

(T_J = 25°C Unless Otherwise Specified)

Characteristic Values

		Min.	Typ.	Max.
V_F	I _F = 12A, V _{GE} = 0V			2.1 V
t_{rr}	I _F = 6A, V _{GE} = 0V, -di _F /dt = 100A/μs		1.4	μs
I_{RM}			21	A

Note 1: Pulse test, t ≤ 300μs, duty cycle, d ≤ 2%.

Littelfuse reserves the right to change limits, test conditions and dimensions.

IXYS MOSFETs and IGBTs are covered by one or more of the following U.S. patents:

4,835,592	4,931,844	5,049,961	5,237,481	6,162,665	6,404,065 B1	6,683,344	6,727,585	7,005,734 B2	7,157,338B2
4,860,072	5,017,508	5,063,307	5,381,025	6,259,123 B1	6,534,343	6,710,405 B2	6,759,692	7,063,975 B2	
4,881,106	5,034,796	5,187,117	5,486,715	6,306,728 B1	6,583,505	6,710,463	6,771,478 B2	7,071,537	

Fig. 1. Output Characteristics @ $T_J = 25^\circ\text{C}$




Fig. 2. Extended Output Characteristics @ $T_J = 25^\circ\text{C}$




Fig. 3. Output Characteristics @ $T_J = 125^\circ\text{C}$




Fig. 4. Dependence of $V_{CE(sat)}$ on Junction Temperature




Fig. 5. Collector-to-Emitter Voltage vs. Gate-to-Emitter Voltage




Fig. 6. Input Admittance




Fig. 7. Transconductance




Fig. 8. Forward Voltage Drop of Intrinsic Diode




Fig. 9. Gate Charge




Fig. 10. Capacitance




Fig. 11. Reverse-Bias Safe Operating Area




Fig. 12. Maximum Transient Thermal Impedance










Fig. 15. Resistive Turn-on Rise Time vs.
Junction TemperatureFig. 16. Resistive Turn-on Rise Time vs.
Collector CurrentFig. 17. Resistive Turn-on Switching Times vs.
Gate ResistanceFig. 18. Resistive Turn-off Switching Times vs.
Junction TemperatureFig. 19. Resistive Turn-off Switching Times vs.
Collector CurrentFig. 20. Resistive Turn-off Switching Times vs.
Gate Resistance

Fig. 13. Forward-Bias Safe Operating Area
@ $T_C = 25^\circ\text{C}$






Fig. 14. Forward-Bias Safe Operating Area
@ $T_C = 75^\circ\text{C}$




TO-263HV Outline



- 1 = Gate
2 = Emitter
3 = Collector

SYM	INCHES		MILLIMETER	
	MIN	MAX	MIN	MAX
A	.170	.185	4.30	4.70
A1	.000	.008	0.00	0.20
A2	.091	.098	2.30	2.50
b	.028	.035	0.70	0.90
b2	.046	.054	1.18	1.38
C	.018	.024	0.45	0.60
C2	.049	.055	1.25	1.40
D	.354	.370	9.00	9.40
D1	.311	.327	7.90	8.30
D2	.083	.098	2.10	2.50
E	.386	.402	9.80	10.20
E1	.307	.323	7.80	8.20
e1	.200 BSC		5.08 BSC	
(e2)	.163	.174	4.13	4.43
H	.591	.614	15.00	15.60
L	.079	.102	2.00	2.60
L1	.039	.055	1.00	1.40
L3	.010 BSC		0.254 BSC	
(L4)	.071	.087	1.80	2.20

TO-268HV Outline



- 1 - Gate
2 - Emitter
3 - Collector

SYM	INCHES		MILLIMETER	
	MIN	MAX	MIN	MAX
A	.193	.201	4.90	5.10
A1	.106	.114	2.70	2.90
A2	.001	.010	0.02	0.25
b	.045	.057	1.15	1.45
C	.016	.026	0.40	0.65
C2	.057	.063	1.45	1.60
D	.543	.551	13.80	14.00
D1	.465	.476	11.80	12.10
D2	.295	.307	7.50	7.80
D3	.114	.126	2.90	3.20
E	.624	.632	15.85	16.05
E1	.524	.535	13.30	13.60
e	.215 BSC		5.45 BSC	
(e2)	.374	.386	9.50	9.80
H	.736	.752	18.70	19.10
L	.067	.079	1.70	2.00
L2	.039	.045	1.00	1.15
L3	.010 BSC		0.25 BSC	
L4	.150	.161	3.80	4.10