

# HiPerFET™

## Power MOSFETs


### Single Die MOSFET

**IXFN 340N06**

$$\begin{aligned} V_{DSS} &= 60 \text{ V} \\ I_{D25} &= 340 \text{ A} \\ R_{DS(on)} &= 3 \text{ m}\Omega \end{aligned}$$


$$t_{rr} \leq 250 \text{ ns}$$

N-Channel Enhancement Mode  
Avalanche Rated, High dv/dt, Low  $t_{rr}$



| Symbol       | Test Conditions                                                                                                                         | Maximum Ratings  |                        |
|--------------|-----------------------------------------------------------------------------------------------------------------------------------------|------------------|------------------------|
| $V_{DSS}$    | $T_J = 25^\circ\text{C}$ to $150^\circ\text{C}$                                                                                         | 60               | V                      |
| $V_{DGR}$    | $T_J = 25^\circ\text{C}$ to $150^\circ\text{C}$ ; $R_{GS} = 1 \text{ M}\Omega$                                                          | 60               | V                      |
| $V_{GS}$     | Continuous                                                                                                                              | $\pm 20$         | V                      |
| $V_{GSM}$    | Transient                                                                                                                               | $\pm 30$         | V                      |
| $I_{D25}$    | $T_C = 25^\circ\text{C}$ , Chip capability                                                                                              | 340              | A                      |
| $I_{L(RMS)}$ | Terminal current limit                                                                                                                  | 100              | A                      |
| $I_{DM}$     | $T_C = 25^\circ\text{C}$ , pulse width limited by $T_{JM}$                                                                              | 1360             | A                      |
| $I_{AR}$     | $T_C = 25^\circ\text{C}$                                                                                                                | 200              | A                      |
| $E_{AR}$     | $T_C = 25^\circ\text{C}$                                                                                                                | 64               | mJ                     |
| $E_{AS}$     | $T_C = 25^\circ\text{C}$                                                                                                                | 4                | J                      |
| dv/dt        | $I_S \leq I_{DM}$ , di/dt $\leq 100 \text{ A}/\mu\text{s}$ , $V_{DD} \leq V_{DSS}$ ,<br>$T_J \leq 150^\circ\text{C}$ , $R_G = 2 \Omega$ | 5                | V/ns                   |
| $P_D$        | $T_C = 25^\circ\text{C}$                                                                                                                | 700              | W                      |
| $T_J$        |                                                                                                                                         | -55 ... +150     | $^\circ\text{C}$       |
| $T_{JM}$     |                                                                                                                                         | 150              | $^\circ\text{C}$       |
| $T_{stg}$    |                                                                                                                                         | -55 ... +150     | $^\circ\text{C}$       |
| $V_{ISOL}$   | 50/60 Hz, RMS $t = 1 \text{ min}$<br>$I_{ISOL} \leq 1 \text{ mA}$ $t = 1 \text{ s}$                                                     | 2500<br>3000     | V~<br>V~               |
| $M_d$        | Mounting torque<br>Terminal connection torque                                                                                           | 1.5/13<br>1.5/13 | Nm/lb.in.<br>Nm/lb.in. |
| Weight       |                                                                                                                                         | 30               | g                      |

miniBLOC, SOT-227 B (IXFN)  
E153432



G = Gate  
S = Source  
D = Drain

Either Source terminal at miniBLOC can be used as Main or Kelvin Source

#### Features

- International standard packages
- miniBLOC, with Aluminium nitride isolation
- Low  $R_{DS(on)}$  HDMOS™ process
- Rugged polysilicon gate cell structure
- Unclamped Inductive Switching (UIS) rated
- Low package inductance
- Fast intrinsic Rectifier

#### Applications


- DC-DC converters
- Battery chargers
- Switched-mode and resonant-mode power supplies
- DC choppers
- Temperature and lighting controls

#### Advantages

- Easy to mount
- Space savings
- High power density

| Symbol       | Test Conditions                                                                                                       | Characteristic Values<br>( $T_J = 25^\circ\text{C}$ , unless otherwise specified) |      |                                     |
|--------------|-----------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|------|-------------------------------------|
|              |                                                                                                                       | min.                                                                              | typ. | max.                                |
| $V_{DSS}$    | $V_{GS} = 0 \text{ V}$ , $I_D = 3 \text{ mA}$                                                                         | 60                                                                                |      | V                                   |
| $V_{GH(th)}$ | $V_{DS} = V_{GS}$ , $I_D = 8 \text{ mA}$                                                                              | 2.0                                                                               |      | 4.0 V                               |
| $I_{GSS}$    | $V_{GS} = \pm 20 \text{ V}_{DC}$ , $V_{DS} = 0$                                                                       |                                                                                   |      | $\pm 200 \text{ nA}$                |
| $I_{DSS}$    | $V_{DS} = V_{DSS}$ , $V_{GS} = 0 \text{ V}$                                                                           |                                                                                   |      | $100 \mu\text{A}$<br>$2 \text{ mA}$ |
| $R_{DS(on)}$ | $V_{GS} = 10 \text{ V}$ , $I_D = 100 \text{ A}$<br>Pulse test, $t \leq 300 \mu\text{s}$ ,<br>duty cycle $d \leq 2 \%$ |                                                                                   |      | 3 m $\Omega$                        |

| Symbol       | Test Conditions                                                                                         | Characteristic Values<br>( $T_J = 25^\circ\text{C}$ , unless otherwise specified) |       |         |
|--------------|---------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-------|---------|
|              |                                                                                                         | min.                                                                              | typ.  | max.    |
| $g_{fs}$     | $V_{DS} = 10\text{ V}; I_D = 60\text{ A}$ , pulse test                                                  | 80                                                                                | 105   | S       |
| $C_{iss}$    | $V_{GS} = 0\text{ V}, V_{DS} = 25\text{ V}, f = 1\text{ MHz}$                                           |                                                                                   | 16800 | pF      |
| $C_{oss}$    |                                                                                                         |                                                                                   | 8200  | pF      |
| $C_{rss}$    |                                                                                                         |                                                                                   | 5000  | pF      |
| $t_{d(on)}$  | $V_{GS} = 10\text{ V}, V_{DS} = 0.5 \cdot V_{DSS}, I_D = 100\text{ A}$<br>$R_G = 2\ \Omega$ (External), |                                                                                   | 140   | ns      |
| $t_r$        |                                                                                                         |                                                                                   | 95    | ns      |
| $t_{d(off)}$ |                                                                                                         |                                                                                   | 200   | ns      |
| $t_f$        |                                                                                                         |                                                                                   | 33    | ns      |
| $Q_{g(on)}$  | $V_{GS} = 10\text{ V}, V_{DS} = 50\text{ V}, I_D = 100\text{ A}$                                        |                                                                                   | 600   | nC      |
| $Q_{gs}$     |                                                                                                         |                                                                                   | 110   | nC      |
| $Q_{gd}$     |                                                                                                         |                                                                                   | 300   | nC      |
| $R_{thJC}$   |                                                                                                         |                                                                                   | 0.05  | 0.18 KW |
| $R_{thCK}$   |                                                                                                         |                                                                                   |       | KW      |

**miniBLOC, SOT-227 B**

**M4 screws (4x) supplied**

| Dim. | Millimeter |       | Inches |       |
|------|------------|-------|--------|-------|
|      | Min.       | Max.  | Min.   | Max.  |
| A    | 31.50      | 31.88 | 1.240  | 1.255 |
| B    | 7.80       | 8.20  | 0.307  | 0.323 |
| C    | 4.09       | 4.29  | 0.161  | 0.169 |
| D    | 4.09       | 4.29  | 0.161  | 0.169 |
| E    | 4.09       | 4.29  | 0.161  | 0.169 |
| F    | 14.91      | 15.11 | 0.587  | 0.595 |
| G    | 30.12      | 30.30 | 1.186  | 1.193 |
| H    | 38.00      | 38.23 | 1.496  | 1.505 |
| J    | 11.68      | 12.22 | 0.460  | 0.481 |
| K    | 8.92       | 9.60  | 0.351  | 0.378 |
| L    | 0.76       | 0.84  | 0.030  | 0.033 |
| M    | 12.60      | 12.85 | 0.496  | 0.506 |
| N    | 25.15      | 25.42 | 0.990  | 1.001 |
| O    | 1.98       | 2.13  | 0.078  | 0.084 |
| P    | 4.95       | 5.97  | 0.195  | 0.235 |
| Q    | 26.54      | 26.90 | 1.045  | 1.059 |
| R    | 3.94       | 4.42  | 0.155  | 0.174 |
| S    | 4.72       | 4.85  | 0.186  | 0.191 |
| T    | 24.59      | 25.07 | 0.968  | 0.987 |
| U    | -0.05      | 0.1   | -0.002 | 0.004 |

| Symbol   | Test Conditions                                                                                                | Characteristic Values<br>( $T_J = 25^\circ\text{C}$ , unless otherwise specified) |      |               |
|----------|----------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|------|---------------|
|          |                                                                                                                | min.                                                                              | typ. | max.          |
| $I_s$    | $V_{GS} = 0\text{ V}$                                                                                          |                                                                                   |      | 340 A         |
| $I_{SM}$ | Repetitive;<br>pulse width limited by $T_{JM}$                                                                 |                                                                                   |      | 1360 A        |
| $V_{SD}$ | $I_F = 100\text{ A}, V_{GS} = 0\text{ V}$ ,<br>Pulse test, $t \leq 300\ \mu\text{s}$ , duty cycle $d \leq 2\%$ |                                                                                   |      | 1.2 V         |
| $t_{rr}$ | $I_F = 50\text{ A}, -di/dt = 100\text{ A}/\mu\text{s}, V_R = 40\text{ V}; T_J = 25^\circ\text{C}$              | 1.4                                                                               | 8    | 250 ns        |
| $Q_{RM}$ |                                                                                                                |                                                                                   |      | $\mu\text{C}$ |
| $I_{RM}$ |                                                                                                                |                                                                                   |      | A             |

IXYS reserves the right to change limits, test conditions, and dimensions.

 IXYS MOSFETS and IGBTs are covered by one or more of the following U.S. patents:
 

|           |           |           |           |           |           |
|-----------|-----------|-----------|-----------|-----------|-----------|
| 4,835,592 | 4,881,106 | 5,017,508 | 5,049,961 | 5,187,117 | 5,486,715 |
| 4,850,072 | 4,931,844 | 5,034,796 | 5,063,307 | 5,237,481 | 5,381,025 |



---

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics).