




RESISTANCE @ $+25^{\circ}\text{C}$ = $1,000,000 \Omega \pm 10\%$
 RESISTANCE/TEMPERATURE CURVE = "V3"
 BETA " β " (0 TO $+50^{\circ}\text{C}$) = 4,369°K NOMINAL
 TEMPERATURE COEFFICIENT @ $+25^{\circ}\text{C}$ = $-4.93\%/^{\circ}\text{C}$ NOMINAL
 DISSIPATION CONSTANT = 2 mW/ $^{\circ}\text{C}$ NOMINAL
 THERMAL TIME CONSTANT = 8 SECONDS MAXIMUM
 MAXIMUM TEMPERATURE RATING = $+220^{\circ}\text{C}$

REV	REVISION RECORD	DATE	APP
---	ISO RELEASE	08/26/08	DD
"A"	CHANGED DIMENSIONS	08/26/08	DD

SCALE NONE	U.S. SENSOR corp. www.ussensor.com 714-639-1000 © COPYRIGHT
DRAWN BY DAN DANKERT	
DATE 06/29/00	NTC THERMISTOR P/N SM105V3K
REV. "A"	
LAYER 0 OF 1	