




RESISTANCE @ +25°C = 10,000 Ω $\pm$ 1%
 RESISTANCE/TEMPERATURE CURVE= "J"
 TEMPERATURE COEFFICIENT @ +25°C = -4.4%/°C NOMINAL
 BETA " β " (0 TO +50°C) = 3,892°K NOMINAL
 MAXIMUM TEMPERATURE RATING = +125°C

LEAD WIRE: 30 AWG (0.010" DIAMETER), SINGLE CONDUCTOR,
 SOLID CONDUCTOR, KYNAR INSULATED

*** ROHS COMPLIANT ***

SEE MANUFACTURING SPECIFICATION (LAYER 1)

NONE	RELEASE TO PRODUCTION	01/11/12	DD
REV	REVISION RECORD	DATE	APP

SCALE	NONE	© COPYRIGHT	
DRAWN BY	DAN DANKERT	U.S. SENSOR CORP.	
DATE	01/11/12	714-639-1000 www.ussensor.com	
REV	NONE	THERMISTOR PROBE	
LAYER	0 OF 2	P/N USP12840	