


| PART NUMBER | PACKAGING   |
|-------------|-------------|
| LR222E0J-1  | BULK        |
| LR222E0J-2  | TAPE & REEL |

RESISTANCE @ +25°C = 2,200  $\Omega$   $\pm$  5%  
 RESISTANCE/TEMPERATURE CURVE = SEE LR222E0J R-T TABLE  
 BETA " $\beta$ " (+25 TO +85°C) = 3,400°K NOMINAL  
 POWER RATING = 320 mW  
 TEMPERATURE RATING = -40 TO +125°C

PACKAGING: SEE TABLE

ROHS COMPLIANT

SEE MANUFACTURING SPECIFICATION (LAYER 1)



|      |                       |          |     |
|------|-----------------------|----------|-----|
| NONE | RELEASE TO PRODUCTION | 04/27/17 | DD  |
| REV  | REVISION RECORD       | DATE     | APP |

|          |             |                                                                   |  |
|----------|-------------|-------------------------------------------------------------------|--|
| SCALE    | NONE        | U.S. SENSOR corp.<br>© COPYRIGHT<br>714-639-1000 www.ussensor.com |  |
| DRAWN BY | DAN DANKERT |                                                                   |  |
| DATE     | 04/27/17    | NTC CHIP THERMISTOR                                               |  |
| REV.     | NONE        | P/N LR222E0J-                                                     |  |
| LAYER    | 0 OF 2      |                                                                   |  |