




RESISTANCE @ +25°C = 300 Ω $\pm$ 10%
 RESISTANCE/TEMPERATURE CURVE = "F"
 BETA " β " (0 TO +50°C) = 3,419°K NOMINAL
 TEMPERATURE COEFFICIENT @ +25°C = -3.86%/°C NOMINAL
 DISSIPATION CONSTANT = 3 mW/°C NOMINAL
 THERMAL TIME CONSTANT = 20 SECONDS NOMINAL
 MAXIMUM TEMPERATURE RATING = +150°C

REV	REVISION RECORD	DATE	APP
NONE	RELEASE TO PRODUCTION	06/01/09	DD

SCALE	NONE	U.S. SENSOR CORP. 1832 W. COLLINS AVE. ORANGE, CA . 92867 714-639-1000 www.ussensor.com	
DRAWN BY	DAN DANKERT		
DATE	06/01/09		
REV.	NONE		
LAYER	0 OF 1	NTC THERMISTOR	
		P/N DC301F3K	