

## SE-325 NEUTRAL-GROUNDING-RESISTOR MONITOR SETTING

Substation Identification: \_\_\_\_\_

Secondary Voltage: \_\_\_\_\_

SE-325 Model Number and Serial Number: \_\_\_\_\_

### Ground-Fault Trip Level

CHECK ONE	GF SETTING
<input type="checkbox"/>	4 A
<input checked="" type="checkbox"/>	2 A
<input type="checkbox"/>	0.5 A

### Ground-Fault Trip Time

Setting: \_\_\_\_\_ seconds

### Output Contact Mode of Operation

CHECK ONE	MODE SETTING
<input type="checkbox"/>	SH (Shunt Trip)
<input checked="" type="checkbox"/>	UV (Undervoltage Trip)

### Sensing Resistor

CHECK ONE	MODEL
<input type="checkbox"/>	ER-600VC
<input checked="" type="checkbox"/>	ER-5KV
<input type="checkbox"/>	ER-15KV
<input type="checkbox"/>	ER-25KV
<input type="checkbox"/>	ER-35KV

### RES

CHECK ONE	NGR RESISTANCE
<input type="checkbox"/>	100K
<input checked="" type="checkbox"/>	20K

### Remote Indication

CHECK ONE	MODEL
<input type="checkbox"/>	None
<input checked="" type="checkbox"/>	RK-13 Relay Interface Module
<input type="checkbox"/>	RK-302 Remote Indication and Reset Kit
<input checked="" type="checkbox"/>	RK-325 Remote Indication and Reset Assembly
<input type="checkbox"/>	RK-325I Remote Indication Assembly

### RES Trip Lvel (Vac)

For RES = 100K

Range is 100 to 2000 Vac

Setting: \_\_\_\_\_

For RES = 20K

Range is 20 to 400 Vac

Setting: \_\_\_\_\_

### NGR Ratings

Current: \_\_\_\_\_ A

Voltage: \_\_\_\_\_ V

### Current Transformer

CHECK ONE	CT SIZE
<input type="checkbox"/>	CT200, 56 mm (2.2") Inner Diameter
<input checked="" type="checkbox"/>	CT200L, 89 mm (3.5") Inner Diameter