



- NOTES:
1. MAX. RATING (SEE CHART), 32 VOLTS AT A MAXIMUM OPERATING TEMPERATURE OF 82° C.
  2. BODY MATERIAL: ALCRYN, BLACK  
COVER MATERIAL: ALCRYN, BLACK
  3. COVER TETHER IS SLID ON EITHER WIRE LEAD AND SEATED IN BODY GROOVE.
  4. FUSEHOLDER IS SHIPPED WITH COVER ATTACHED BUT NOT SNAPPED ON THE BODY.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

DENOTES CRITICAL CHARACTERISTICS.

DENOTES CPK DIMENSIONS.-MINIMUM CPK VALUE

DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE AND PROCEDURE FOR MEASUREMENT

(ST) DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE AND PROCEDURE FOR MEASUREMENT

DENOTES CP DIMENSIONS.-MINIMUM CP VALUE

DENOTES DIMENSIONS WITHIN THE DIMENSIONAL LIMITATIONS

AND SHALL BE WITHIN THE DIMENSIONAL LIMITATIONS

FOR MAXIMUM TOOL LIFE.

NO		COMPONENT NO	DESCRIPTION	QTY/M	U/M
<b>BILL OF MATERIAL</b>					
COPIES TO		MATL SPEC		FINISH	
1	9	18	DRW	PJM	DATE 9/4/01
2	10	19	CHK	DATE	SCALE 1:1
3	12	20	APPD	DATE	SUPER DRW
4	13	21	DATE	DATE	RAW STK WT
5	14	23	DATE	DATE	LBS/M
6	15	33	DATE	DATE	TOLERANCE UNLESS OTHERWISE SPECIFIED
7	16	43	DATE	DATE	TWO PLACE DEC ±.01
8	17	53	DATE	DATE	THREE PLACE DEC ±.005
<b>TITLE</b>					
MINIFUSE HOLDER, IN LINE					
LTR		REVISION		CHK	APD
A	60655	RELEASE 9/4/01 PJM			

DES PLAINES, ILLINOIS 60016  
 DRAWING NO. SERIES OUTLINE  
 A 01530028Z

UNCONTROLLED DOCUMENT