



- NOTES:  
 1). RATING: NO: 14Vdc/35A  
 NC: 14Vdc/20A  
 2). TEMPERATURE RANGE: -40C TO 125C  
 3). RELAY IS FLUX-TIGHT.  
 4). ALL DIMENSIONS SHOWN FOR REFERENCE ONLY.

# METRIC COMPONENT

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
<b>BILL OF MATERIAL</b>				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [ ] ARE INCHES				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.				
⊙	DENOTES CRITICAL CHARACTERISTICS.			
CPK	DENOTES CPK DIMENSIONS. -MINIMUM CPK VALUE			
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS			
CP	DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE			

COPIES TO		MATL SPEC	
1	9	18	FINISH
2	10	19	DRW
3	12	20	CAD
4	13	21	CHK
5	14	23	APPD
6	15	33	SCALE
7	16	43	DATE
8	17	53	DATE

  

LTR	DATE	REVISION	CHK	APD
A	06/24/09	000716ER RELEASED	CAD	
B	08/08/11	503010ERA-SEE ERN GMB		
C	04/18/12	504753ECA ADD DIODE VERSION EJIN		

  

TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-fH)	UP TO	OVER	UP TO	OVER	UP TO	OVER	UP TO	OVER	UP TO	OVER	GRAMS/PIECE
DIMENSION	0.5	- 3	3	- 6	6	- 30	30	- 120	120	- 400	400
TOLERANCE	±0.05		±0.05		±0.1		±0.15		±0.2		

  

TITLE		SINGLE POLE, DOUBLE THROW	
MICRO RELAY		MICRO RELAY	

  

REVISION	DRWG. NO.
C	02040090Z

  

3RD ANGLE PROJECTION

**Littelfuse**  
 DES PLAINES, ILLINOIS 60016