




THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.

PART NUMBER	DESCRIPTION
178.6165.0001	HOLDER - FLR (ATO) PCB 80V 4-PIN 100 PC
178.6165.0002	HOLDER - FLR (ATO) PCB 80V 4-PIN 500 PC ^(H)

REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	C	IN CAD GEZ.	ULB	01/10/00
	D	AEND.Nr: 287	MAK	04/16/02
	E	AEND.Nr: 0058	HOEP	04/06/05
	F	AEND.Nr: 20113DN1	HOEP	06/03/06
	G	510213ECA-REDRAW IN UG	OPL	07/03/14
	H	ECN #523216: CLARIFY DIMENSIONS, ADD PN, UPDATE TEMPLATE		01/06/2021 S.CASTILLO



HOLE PATTERN



- NOTES:
- MATERIAL:
 - ** HOUSING: THERMOPLASTIC
 - ** DFK1-TERMINALS F SOLDERING: Cu-ALLOY, Ag- PLATED
 - GENERAL TOLERANCES: DIN 7168-m

DIMENSIONS ARE SHOWN IN MILLIMETERS. DIMENSIONS AND TOLERANCES ARE DEFINED ACCORDING TO ANSI/ASME Y14.5-1994.				
●	FIT FUNCTION CRITICAL CHARACTERISTICS SYMBOL			
<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL			
CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE			
(ST)	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS			
CP	DENOTES CP DIMENSIONS - MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE			
DIMENSION: MM TOLERANCES UNLESS OTHERWISE SPECIFIED ONE PLACE DECIMAL ± 0.5 THREE PLACES DECIMAL ± 0.100 TWO PLACES DECIMAL ± 0.20 ANGULAR $\pm 2'$				
NAME	DATE	 Expertise Applied Answers Delivered		
DRAWN	OPL			03/14/14
CHECKED	-			-
FORM NO: CVP-PE40-0006 REV A		TITLE		
THIRD ANGLE PROJECTION		HOLDER-FLR (ATO) PCV 80V 4-PIN		
SIZE	DWG. NO.	REV.		
C	178.6165.0000	H		
DO NOT SCALE DRAWING		SCALE 5:1	SHEET 1 OF 1	