


## HiPerFET™ Power MOSFETs Q-Class


## IXFN50N80Q2

N-Channel Enhancement Mode  
Avalanche Rated, Low  $Q_g$ , Low Intrinsic  $R_g$   
High  $dV/dt$ , Low  $t_{rr}$



$$\begin{aligned} V_{DSS} &= 800V \\ I_{D25} &= 50A \\ R_{DS(on)} &\leq 160m\Omega \\ t_{rr} &\leq 300ns \end{aligned}$$

miniBLOC, SOT-227  
E153432



G = Gate      D = Drain  
S = Source

Either Source Terminal S can be used as the Source Terminal or the Kelvin Source ( Gate Return ) Terminal.

| Symbol     | Test Conditions                                                           | Maximum Ratings |                  |
|------------|---------------------------------------------------------------------------|-----------------|------------------|
| $V_{DSS}$  | $T_J = 25^\circ\text{C}$ to $150^\circ\text{C}$                           | 800             | V                |
| $V_{DGR}$  | $T_J = 25^\circ\text{C}$ to $150^\circ\text{C}$ , $R_{GS} = 1M\Omega$     | 800             | V                |
| $V_{GSS}$  | Continuous                                                                | $\pm 30$        | V                |
| $V_{GSM}$  | Transient                                                                 | $\pm 40$        | V                |
| $I_{D25}$  | $T_C = 25^\circ\text{C}$                                                  | 50              | A                |
| $I_{DM}$   | $T_C = 25^\circ\text{C}$ , Pulse Width Limited by $T_{JM}$                | 200             | A                |
| $I_A$      | $T_C = 25^\circ\text{C}$                                                  | 50              | A                |
| $E_{AS}$   | $T_C = 25^\circ\text{C}$                                                  | 5               | J                |
| $dv/dt$    | $I_S \leq I_{DM}$ , $V_{DD} \leq V_{DSS}$ , $T_J \leq 150^\circ\text{C}$  | 20              | V/ns             |
| $P_D$      | $T_C = 25^\circ\text{C}$                                                  | 1135            | W                |
| $T_J$      |                                                                           | -55 ... +150    | $^\circ\text{C}$ |
| $T_{JM}$   |                                                                           | 150             | $^\circ\text{C}$ |
| $T_{stg}$  |                                                                           | -55 ... +150    | $^\circ\text{C}$ |
| $T_L$      | 1.6mm (0.062 in.) from Case for 10s                                       | 300             | $^\circ\text{C}$ |
| $T_{SOLD}$ | Plastic Body for 10s                                                      | 260             | $^\circ\text{C}$ |
| $V_{ISOL}$ | 50/60 Hz, RMS $t = 1$ minute<br>$I_{ISOL} \leq 1\text{mA}$ $t = 1$ second | 2500<br>3000    | V~<br>V~         |
| $M_d$      | Mounting Torque                                                           | 1.5/13          | Nm/lb.in.        |
|            | Terminal Connection Torque                                                | 1.3/11.5        | Nm/lb.in.        |
| Weight     |                                                                           | 30              | g                |

| Symbol       | Test Conditions<br>( $T_J = 25^\circ\text{C}$ , Unless Otherwise Specified) | Characteristic Values |      |                          |
|--------------|-----------------------------------------------------------------------------|-----------------------|------|--------------------------|
|              |                                                                             | Min.                  | Typ. | Max.                     |
| $BV_{DSS}$   | $V_{GS} = 0V$ , $I_D = 1\text{mA}$                                          | 800                   |      | V                        |
| $V_{GS(th)}$ | $V_{DS} = V_{GS}$ , $I_D = 8\text{mA}$                                      | 3.0                   |      | 5.5 V                    |
| $I_{GSS}$    | $V_{GS} = \pm 30V$ , $V_{DS} = 0V$                                          |                       |      | $\pm 200$ nA             |
| $I_{DSS}$    | $V_{DS} = V_{DSS}$ , $V_{GS} = 0V$<br>$T_J = 125^\circ\text{C}$             |                       |      | 50 $\mu\text{A}$<br>3 mA |
| $R_{DS(on)}$ | $V_{GS} = 10V$ , $I_D = 0.5 \cdot I_{D25}$ , Note 1                         |                       |      | 160 m $\Omega$           |

### Features

- International Standard Package
- miniBLOC, with Aluminium Nitride Isolation
- Isolation Voltage 2500 V~
- High Current Handling Capability
- Fast Intrinsic Rectifier
- Avalanche Rated
- Low  $R_{DS(on)}$

### Advantages

- Easy to Mount
- Space Savings
- High Power Density

### Applications

- Switch-Mode and Resonant-Mode Power Supplies >500kHz Switching
- DC-DC Converters
- DC Choppers
- Pulse Generation
- Laser Drivers

| Symbol       | Test Conditions<br>( $T_J = 25^\circ\text{C}$ , Unless Otherwise Specified)                                                                        | Characteristic Values |      |                         |
|--------------|----------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|------|-------------------------|
|              |                                                                                                                                                    | Min.                  | Typ. | Max.                    |
| $g_{fs}$     | $V_{DS} = 10\text{V}$ , $I_D = 0.5 \cdot I_{D25}$ , Note 1                                                                                         | 32                    | 48   | S                       |
| $C_{iss}$    | $V_{GS} = 0\text{V}$ , $V_{DS} = 25\text{V}$ , $f = 1\text{MHz}$                                                                                   |                       | 13.5 | nF                      |
| $C_{oss}$    |                                                                                                                                                    |                       | 1180 | pF                      |
| $C_{rss}$    |                                                                                                                                                    |                       | 213  | pF                      |
| $t_{d(on)}$  | <b>Resistive Switching Times</b><br>$V_{GS} = 10\text{V}$ , $V_{DS} = 0.5 \cdot V_{DSS}$ , $I_D = 0.5 \cdot I_{D25}$<br>$R_G = 1\Omega$ (External) |                       | 26   | ns                      |
| $t_r$        |                                                                                                                                                    |                       | 25   | ns                      |
| $t_{d(off)}$ |                                                                                                                                                    |                       | 60   | ns                      |
| $t_f$        |                                                                                                                                                    |                       | 13   | ns                      |
| $Q_{g(on)}$  | $V_{GS} = 10\text{V}$ , $V_{DS} = 0.5 \cdot V_{DSS}$ , $I_D = 0.5 \cdot I_{D25}$                                                                   |                       | 260  | nC                      |
| $Q_{gs}$     |                                                                                                                                                    |                       | 56   | nC                      |
| $Q_{gd}$     |                                                                                                                                                    |                       | 120  | nC                      |
| $R_{thJC}$   |                                                                                                                                                    |                       |      | 0.11 $^\circ\text{C/W}$ |
| $R_{thCS}$   |                                                                                                                                                    |                       | 0.05 | $^\circ\text{C/W}$      |

## Source-Drain Diode

| Symbol   | Test Conditions<br>( $T_J = 25^\circ\text{C}$ , Unless Otherwise Specified)                            | Characteristic Values |      |               |
|----------|--------------------------------------------------------------------------------------------------------|-----------------------|------|---------------|
|          |                                                                                                        | Min.                  | Typ. | Max.          |
| $I_S$    | $V_{GS} = 0\text{V}$                                                                                   |                       |      | 50 A          |
| $I_{SM}$ | Repetitive, Pulse Width Limited by $T_{JM}$                                                            |                       |      | 200 A         |
| $V_{SD}$ | $I_F = 50\text{A}$ , $V_{GS} = 0\text{V}$ , Note 1                                                     |                       |      | 1.5 V         |
| $t_{rr}$ | $I_F = 25\text{A}$ , $V_{GS} = 0\text{V}$<br>$-di/dt = 100\text{A}/\mu\text{s}$<br>$V_R = 100\text{V}$ |                       |      | 300 ns        |
| $Q_{RM}$ |                                                                                                        |                       | 1.1  | $\mu\text{C}$ |
| $I_{RM}$ |                                                                                                        |                       | 8.0  | A             |

Note 1. Pulse test,  $t \leq 300\mu\text{s}$ , duty cycle,  $d \leq 2\%$ .

## SOT-227B (IXFN) Outline









(M4 screws (4x) supplied)

| SYM | INCHES |       | MILLIMETERS |       |
|-----|--------|-------|-------------|-------|
|     | MIN    | MAX   | MIN         | MAX   |
| A   | 1.240  | 1.255 | 31.50       | 31.88 |
| B   | .307   | .323  | 7.80        | 8.20  |
| C   | .161   | .169  | 4.09        | 4.29  |
| D   | .161   | .169  | 4.09        | 4.29  |
| E   | .161   | .169  | 4.09        | 4.29  |
| F   | .587   | .595  | 14.91       | 15.11 |
| G   | 1.186  | 1.193 | 30.12       | 30.30 |
| H   | 1.496  | 1.505 | 38.00       | 38.23 |
| J   | .460   | .481  | 11.68       | 12.22 |
| K   | .351   | .378  | 8.92        | 9.60  |
| L   | .030   | .033  | 0.76        | 0.84  |
| M   | .496   | .506  | 12.60       | 12.85 |
| N   | .990   | 1.001 | 25.15       | 25.42 |
| O   | .078   | .084  | 1.98        | 2.13  |
| P   | .195   | .235  | 4.95        | 5.97  |
| Q   | 1.045  | 1.059 | 26.54       | 26.90 |
| R   | .155   | .174  | 3.94        | 4.42  |
| S   | .186   | .191  | 4.72        | 4.85  |
| T   | .968   | .987  | 24.59       | 25.07 |
| U   | -.002  | .004  | -0.05       | 0.1   |


IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.

IXYS MOSFETs and IGBTs are covered by one or more of the following U.S. patents:


|           |           |           |           |              |              |              |              |              |             |
|-----------|-----------|-----------|-----------|--------------|--------------|--------------|--------------|--------------|-------------|
| 4,835,592 | 4,931,844 | 5,049,961 | 5,237,481 | 6,162,665    | 6,404,065 B1 | 6,683,344    | 6,727,585    | 7,005,734 B2 | 7,157,338B2 |
| 4,850,072 | 5,017,508 | 5,063,307 | 5,381,025 | 6,259,123 B1 | 6,534,343    | 6,710,405 B2 | 6,759,692    | 7,063,975 B2 |             |
| 4,881,106 | 5,034,796 | 5,187,117 | 5,486,715 | 6,306,728 B1 | 6,583,505    | 6,710,463    | 6,771,478 B2 | 7,071,537    |             |

**Fig. 1. Output Characteristics @  $T_J = 25^\circ\text{C}$** 

**Fig. 2. Extended Output Characteristics @  $T_J = 25^\circ\text{C}$** 

**Fig. 3. Output Characteristics @  $T_J = 125^\circ\text{C}$** 

**Fig. 4.  $R_{DS(on)}$  Normalized to  $I_D = 25\text{A}$  Value vs. Junction Temperature**

**Fig. 5.  $R_{DS(on)}$  Normalized to  $I_D = 25\text{A}$  Value vs. Drain Current**

**Fig. 6. Maximum Drain Current vs. Case Temperature**



**Fig. 7. Input Admittance**




**Fig. 8. Transconductance**




**Fig. 9. Forward Voltage Drop of Intrinsic Diode**




**Fig. 10. Gate Charge**



**Fig. 11. Capacitance**



**Fig. 12. Maximum Transient Thermal Impedance**





---

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics).