




RESISTANCE @ +25°C = 10,000 Ω $\pm$ 5%
 RESISTANCE/TEMPERATURE CURVE = "J"
 TEMPERATURE COEFFICIENT @ +25°C = -4.4%/°C NOMINAL
 MAXIMUM TEMPERATURE RATING = +105°C

LEAD WIRES: 28 AWG, STRANDED CONDUCTOR,
 SINGLE CONDUCTOR, PVC INSULATED

SEE MANUFACTURING SPECIFICATION (LAYER 1)

"A"	LEAD WIRE LENGTH WAS 3" $\pm$ 0.50"	09/21/10	DD
NONE	RELEASE TO PRODUCTION	04/06/10	DD
REV	REVISION RECORD		DATE APP

SCALE	NONE	U.S. SENSOR CORP. 1832 W. COLLINS AVE. ORANGE, CA. 92867 714-639-1000 www.ussensor.com NTC THERMISTOR PROBE P/N USP10997	
DRAWN BY	DAN DANKERT		
DATE	04/06/10		
REV.	"A"		
LAYER	0 OF 2		