


# PAL Fuses - 283B Series

## Rated 32 V DC

RoHS

### Specifications

<b>Voltage Rating:</b>	32 V DC
<b>Current Cycling:</b>	24°C
<b>Operating Temperature Range:</b>	-40°C to +125°C
<b>Complies with</b>	JASO 0612



PAL Fuses - 283B Series

### Description

Many Japanese automakers use 283B Series Auto Link PAL fuses as original equipment. These bolt-down cartridge fuses withstand extreme temperatures while protecting circuits for alternators and starters. During tests, each of the 283B Series PAL fuses met its performance requirements when receiving 50 % of its ampere rating for 10 000 cycles when current flowed for 5 minutes and was shut off for 10 minutes. The tests were conducted while the temperature of the bolt-down cartridge fuse was 24 °C.

### Features & Benefits

- Color coding indicates ampere rating
- Transparent covers make it easier to see when fuses blow
- Bolt securely with two mounting holes

### Applications

- Cars made in Japan and the United States

### Ordering Information

Part Number	Package Size
0283xxx.MXJ-B	1000

# PAL Fuses - 283B Series

Rated 32 V DC


## Ratings

Part Number	Current Rating (A)	Body Color
0283020.MXJ-B	20	LIGHT BLUE
0283030.MXJ-B	30	PINK
0283040.MXJ-B	40	GREEN
0283050.MXJ-B	50	RED
0283060.MXJ-B	60	YELLOW
0283070.MXJ-B	70	BROWN
0283080.MXJ-B	80	BLACK
0283100.MXJ-B	100	BLUE
0283120.MXJ-B	120	WHITE
0283140.MXJ-B	140	REDDISH BROWN

(Average Initial Measurements)

## Dimensions

Dimensions in mm



# PAL Fuses - 283B Series

Rated 32 V DC

## Time-Current Characteristics

% of Rating	Opening Time Min / Max (s)
110	14,400
200	5 / 100
350	0.2 / 7
600	0.040 / 1