




RESISTANCE @ +25°C = 50,000 Ω $\pm$ 10%
 RESISTANCE/TEMPERATURE CURVE = "J"
 BETA " β " (0 TO +50°C) = 3,892°K NOMINAL
 TEMPERATURE COEFFICIENT @ +25°C = -4.4%/°C NOMINAL
 DISSIPATION CONSTANT = 1 mW/°C NOMINAL
 THERMAL TIME CONSTANT = 2 SECONDS MAXIMUM
 MAXIMUM TEMPERATURE RATING = +150°C

---	ISO RELEASE	05/05/03	DD
REV	REVISION RECORD	DATE	APP

SCALE	NONE	U.S. SENSOR CORP.	
DRAWN BY	T. SOMERVILLE		
DATE	08/06/92	714-639-1000 www.ussensor.com	
REV.	NONE	NTC CHIP THERMISTOR	
LAYER	0 OF 1	P/N BC503J1K	