


# HiPerFAST™ IGBT IXGR 32N90B2D1 with Fast Diode


## Electrically Isolated Base



$$\begin{aligned} V_{CES} &= 900 \text{ V} \\ I_{C25} &= 47 \text{ A} \\ V_{CE(sat)} &= 2.9 \text{ V} \\ t_{fi\text{typ}} &= 150 \text{ ns} \end{aligned}$$

Symbol	Test Conditions	Maximum Ratings	
$V_{CES}$	$T_J = 25^\circ\text{C}$ to $150^\circ\text{C}$	900	V
$V_{CGR}$	$T_J = 25^\circ\text{C}$ to $150^\circ\text{C}$ ; $R_{GE} = 1 \text{ M}\Omega$	900	V
$V_{GES}$	Continuous	$\pm 20$	V
$V_{GEM}$	Transient	$\pm 30$	V
$I_{C25}$	$T_C = 25^\circ\text{C}$	47	A
$I_{C110}$	$T_C = 110^\circ\text{C}$	22	A
$I_{CM}$	$T_C = 25^\circ\text{C}$ , 1 ms	200	A
<b>SSOA (RBSOA)</b>	$V_{GE} = 15 \text{ V}$ , $T_{VJ} = 125^\circ\text{C}$ , $R_G = 10 \Omega$ Clamped inductive load: $V_{CL} < 600\text{V}$	$I_{CM} = 64$	A
$P_C$	$T_C = 25^\circ\text{C}$	160	W
$T_J$		-55 ... +150	$^\circ\text{C}$
$T_{JM}$		150	$^\circ\text{C}$
$T_{stg}$		-55 ... +150	$^\circ\text{C}$
Maximum lead temperature for soldering 1.6 mm (0.062 in.) from case for 10 s		300	$^\circ\text{C}$
$V_{ISOL}$	50/60Hz, RMS, T= 1 minute $I_{isol} < 1\text{mA}$	2500 3000	V~ V~
$F_C$	Mounting force	20..120/4.5..26	N/lb
<b>Weight</b>		5	g

ISOPLUS247 (IXGR)  
E153432



### Features

- Electrically isolated mounting tab
- High frequency IGBT
- High current handling capability
- MOS Gate turn-on - drive simplicity

### Applications

- PFC circuits
- Uninterruptible power supplies (UPS)
- Switched-mode and resonant-mode power supplies
- AC motor speed control
- DC servo and robot drives
- DC choppers


### Advantages

- High power density
- Very fast switching speeds for high frequency applications

Symbol	Test Conditions	Characteristic Values ( $T_J = 25^\circ\text{C}$ unless otherwise specified)		
		min.	typ.	max.
$V_{GE(th)}$	$I_C = 250 \mu\text{A}$ , $V_{CE} = V_{GE}$	3.0		5.0 V
$I_{CES}$	$V_{CE} = V_{CES}$ $V_{GE} = 0 \text{ V}$ $T_J = 150^\circ\text{C}$			300 $\mu\text{A}$ 1.5 mA
$I_{GES}$	$V_{CE} = 0 \text{ V}$ , $V_{GE} = \pm 20 \text{ V}$			$\pm 100 \text{ nA}$
$V_{CE(sat)}$	$I_C = I_T$ , $V_{GE} = 15 \text{ V}$ , Note 1 $T_J = 125^\circ\text{C}$		2.1	2.9 V V

Symbol	Test Conditions	Characteristic Values ( $T_J = 25^\circ\text{C}$ unless otherwise specified)		
		min.	typ.	max.
$g_{fs}$	$I_C = I_T; V_{CE} = 10\text{ V}$	18	28	S
$C_{ies}$	$V_{CE} = 25\text{ V}, V_{GE} = 0\text{ V}, f = 1\text{ MHz}$		1790	pF
$C_{oes}$			146	pF
$C_{res}$			49	pF
$Q_g$	$I_C = I_T, V_{GE} = 15\text{ V}, V_{CE} = 0.5 V_{CES}$		89	nC
$Q_{ge}$			15	nC
$Q_{gc}$			34	nC
$t_{d(on)}$	Inductive load, $T_J = 25^\circ\text{C}$ $I_C = I_T, V_{GE} = 15\text{ V}$ $V_{CE} = 720\text{ V}, R_G = R_{off} = 5\ \Omega$		20	ns
$t_{ri}$			22	ns
$t_{d(off)}$			260	400 ns
$t_{fi}$			150	ns
$E_{off}$			2.2	4.5 mJ
$t_{d(on)}$	Inductive load, $T_J = 125^\circ\text{C}$ $I_C = I_T, V_{GE} = 15\text{ V}$ $V_{CE} = 720\text{ V}, R_G = R_{off} = 5\ \Omega$		20	ns
$t_{ri}$			22	ns
$E_{on}$			3.8	mJ
$t_{d(off)}$			360	ns
$t_{fi}$			330	ns
$E_{off}$		5.75	mJ	
$R_{thJC}$			0.8	KW
$R_{thCS}$		0.15		KW

### ISOPLUS247 Outline



SYM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	.190	.205	4.83	5.21
A1	.090	.100	2.29	2.54
A2	.075	.085	1.91	2.16
b	.045	.055	1.14	1.40
b1	.075	.084	1.91	2.13
b2	.115	.123	2.92	3.12
C	.024	.031	0.61	0.80
D	.819	.840	20.80	21.34
E	.620	.635	15.75	16.13
e	.215 BSC		5.45 BSC	
L	.780	.800	19.81	20.32
L1	.150	.170	3.81	4.32
Q	.220	.244	5.59	6.20
R	.170	.190	4.32	4.83
S	.520	.540	13.21	13.72
T	.620	.640	15.75	16.26
U	.065	.080	1.65	2.03

- 1- GATE
- 2- COLLECTOR/CATHODE
- 3- EMITTER/ANODE
- 4- NO CONNECTION

NOTE: This drawing will meet all dimensions requirement of JEDEC outline TO-247AD except screw hole.

### Ultrafast Diode

Symbol	Conditions	Maximum Ratings	
$I_{FRMS}$		60	A
$I_{F110}$	$T_C = 110^\circ\text{C}$	22	A







Symbol	Conditions	Characteristic Values		
		min.	typ.	max.
$V_F$	$I_F = 30\text{ A}$ $T_{VJ} = 125^\circ\text{C}$		1.8	2.75 V
$I_{RM}$	$I_F = 50\text{ A}; di_F/dt = -100\text{ A}/\mu\text{s}; T_{VJ} = 100^\circ\text{C}$ $V_R = 100\text{ V}; V_{GE} = 0\text{ V}$		5.5	11.4 A
$t_{rr}$			190	ns
$R_{thJC}$			0.15	1.1 KW
$R_{thCS}$				KW

### Notes:


1. Pulse test: Pulse width < 300  $\mu\text{s}$ , duty cycle < 2 %;
2. Test current  $I_T = 32\text{ A}$ .

IXYS reserves the right to change limits, test conditions, and dimensions.


IXYS MOSFETs and IGBTs are covered by one or more of the following U.S. patents:	4,835,592	4,931,844	5,049,961	5,237,481	6,162,665	6,404,065 B1	6,683,344	6,727,585
	4,850,072	5,017,508	5,063,307	5,381,025	6,259,123 B1	6,534,343	6,710,405 B2	6,759,692
	4,881,106	5,034,796	5,187,117	5,486,715	6,306,728 B1	6,583,505	6,710,463	6,771,478 B2

**Fig. 1. Output Characteristics  
@ 25 °C**

**Fig. 2. Extended Output Characteristics  
@ 25 °C**

**Fig. 3. Output Characteristics  
@ 125 °C**

**Fig. 4. Dependence of  $V_{CE(sat)}$  on  
Temperature**

**Fig. 5. Collector-to-Emitter Voltage  
vs. Gate-to-Emitter voltage**

**Fig. 6. Input Admittance**



**Fig. 7. Transconductance**




**Fig. 8. Gate Charge**




**Fig. 9. Capacitance**



**Fig. 10. Reverse-Bias Safe Operating Area**















**Fig. 11. Maximum Transient Thermal Resistance**



IXYS reserves the right to change limits, test conditions, and dimensions.

IXYS MOSFETs and IGBTs are covered by one or more of the following U.S. patents:	4,835,592	4,931,844	5,049,961	5,237,481	6,162,665	6,404,065 B1	6,683,344	6,727,585
	4,850,072	5,017,508	5,063,307	5,381,025	6,259,123 B1	6,534,343	6,710,405 B2	6,759,692
	4,881,106	5,034,796	5,187,117	5,486,715	6,306,728 B1	6,583,505	6,710,463	6,771,478 B2

**Fig. 12. Dependence of Turn-off Energy Loss on Gate Resistance**

**Fig. 13. Dependence of Turn-on Energy Loss on Gate Resistance**

**Fig. 14. Dependence of Turn-off Energy Loss on Collector Current**

**Fig. 15. Dependence of Turn-on Energy Loss on Collector Current**

**Fig. 16. Dependence of Turn-off Energy Loss on Temperature**

**Fig. 17. Dependence of Turn-on Energy Loss on Temperature**


**Fig. 18. Dependence of Turn-off Switching Time on Gate Resistance**

**Fig. 19. Dependence of Turn-on Switching Time on Gate Resistance**

**Fig. 20. Dependence of Turn-off Switching Time on Collector Current**

**Fig. 21. Dependence of Turn-on Switching Time on Collector Current**

**Fig. 22. Dependence of Turn-off Switching Time on Temperature**

**Fig. 23. Dependence of Turn-on Switching Time on Temperature**


IXYS reserves the right to change limits, test conditions, and dimensions.

IXYS MOSFETs and IGBTs are covered by one or more of the following U.S. patents:	4,835,592	4,931,844	5,049,961	5,237,481	6,162,665	6,404,065 B1	6,683,344	6,727,585
	4,850,072	5,017,508	5,063,307	5,381,025	6,259,123 B1	6,534,343	6,710,405 B2	6,759,692
	4,881,106	5,034,796	5,187,117	5,486,715	6,306,728 B1	6,583,505	6,710,463	6,771,478 B2

Ultrafast Diode Characteristics




Fig. 24. Forward current  $I_F$  versus  $V_F$




Fig. 25. Reverse recovery charge  $Q_r$  versus  $-di_F/dt$




Fig. 26. Peak reverse current  $I_{RM}$  versus  $-di_F/dt$




Fig. 27. Dynamic parameters  $Q_r$ ,  $I_{RM}$  versus  $T_{VJ}$




Fig. 28. Recovery time  $t_{tr}$  versus  $-di_F/dt$




Fig. 29. Peak forward voltage  $V_{FR}$  and  $t_{tr}$  versus  $di_F/dt$




Fig. 30. Transient thermal resistance junction-to-case

Constants for  $Z_{thJC}$  calculation for non-isolated diode (DSEP 30-12A):

i	$R_{thi}$ (K/W)	$t_i$ (s)
1	0.465	0.0052
2	0.179	0.0003
3	0.256	0.0397

Constants for  $Z_{thJC}$  calculation for isolated diode (DSEP 30-12AR):

i	$R_{thi}$ (K/W)	$t_i$ (s)
1	0.368	0.0052
2	0.1417	0.0003
3	0.0295	0.0004
4	0.5604	0.0092



---

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics).