


# PolarP™ Power MOSFETs

P-Channel Enhancement Mode  
Avalanche Rated



**IXTA52P10P**  
**IXTP52P10P**  
**IXTQ52P10P**  
**IXTH52P10P**

$V_{DSS} = -100V$   
 $I_{D25} = -52A$   
 $R_{DS(on)} \leq 50m\Omega$


TO-263 AA (IXTA)




TO-220AB (IXTP)



TO-3P (IXTQ)



TO-247 (IXTH)



G = Gate      D = Drain  
S = Source    Tab = Drain

| Symbol     | Test Conditions  | Maximum Ratings |            |
|------------|--|-----------------|------------|
| $V_{DSS}$  | $T_J = 25^\circ C$ to $150^\circ C$                                | -100            | V          |
| $V_{DGR}$  | $T_J = 25^\circ C$ to $150^\circ C$ , $R_{GS} = 1M\Omega$          | -100            | V          |
| $V_{GSS}$  | Continuous   | $\pm 20$        | V          |
| $V_{GSM}$  | Transient  | $\pm 30$        | V          |
| $I_{D25}$  | $T_C = 25^\circ C$   | - 52            | A          |
| $I_{DM}$   | $T_C = 25^\circ C$ , Pulse Width Limited by $T_{JM}$               | -130            | A          |
| $I_A$      | $T_C = 25^\circ C$   | - 52            | A          |
| $E_{AS}$   | $T_C = 25^\circ C$   | 1.5             | J          |
| dv/dt      | $I_S \leq I_{DM}$ , $V_{DD} \leq V_{DSS}$ , $T_J \leq 150^\circ C$ | 10              | V/ns       |
| $P_D$      | $T_C = 25^\circ C$   | 300             | W          |
| $T_J$      |  | -55 ... +150    | $^\circ C$ |
| $T_{JM}$   |  | 150             | $^\circ C$ |
| $T_{stg}$  |  | -55 ... +150    | $^\circ C$ |
| $T_L$      | 1.6mm (0.062 in.) from Case for 10s                                | 300             | $^\circ C$ |
| $T_{SOLD}$ | Plastic body for 10s   | 260             | $^\circ C$ |
| $M_d$      | Mounting Torque (TO-3P, TO-220, TO-247)                            | 1.13/10         | Nm/lb.in.  |
| Weight     | TO-263   | 2.5             | g          |
|            | TO-220   | 3.0             | g          |
|            | TO-3P  | 5.5             | g          |
|            | TO-247   | 6.0             | g          |

| Symbol       | Test Conditions<br>( $T_J = 25^\circ C$ , Unless Otherwise Specified) | Characteristic Values |      |               |
|--------------|---|-----------------------|------|---------------|
|              |   | Min.                  | Typ. | Max.          |
| $BV_{DSS}$   | $V_{GS} = 0V$ , $I_D = -250\mu A$                                     | -100                  |      | V             |
| $V_{GS(th)}$ | $V_{DS} = V_{GS}$ , $I_D = -250\mu A$                                 | - 2.0                 |      | V             |
| $I_{GSS}$    | $V_{GS} = \pm 20V$ , $V_{DS} = 0V$                                    |                       |      | $\pm 100$ nA  |
| $I_{DSS}$    | $V_{DS} = V_{DSS}$ , $V_{GS} = 0V$<br>$T_J = 125^\circ C$             |                       |      | -10 $\mu A$   |
|              |   |                       |      | -150 $\mu A$  |
| $R_{DS(on)}$ | $V_{GS} = -10V$ , $I_D = 0.5 \cdot I_{D25}$ , Note 1                  |                       |      | 50 m $\Omega$ |

## Features

- International Standard Packages
- Fast Intrinsic Diode
- Dynamic dv/dt Rated
- Avalanche Rated
- Rugged PolarP™ Process
- Low  $Q_G$  and  $R_{ds(on)}$
- Low Drain-to-Tab Capacitance
- Low Package Inductance

## Advantages

- Easy to Mount
- Space Savings
- High Power Density

## Applications

- High-Side Switching
- Push-Pull Amplifiers
- DC Choppers
- Current Regulators
- Automatic Test Equipment

| Symbol       | Test Conditions<br>( $T_J = 25^\circ\text{C}$ , Unless Otherwise Specified)   | Characteristic Values |      |           |
|--------------|---|-----------------------|------|-----------|
|              |   | Min.                  | Typ. | Max.      |
| $g_{fs}$     | $V_{DS} = -10\text{V}$ , $I_D = 0.5 \cdot I_{D25}$ , Note 1   | 12                    | 20   | S         |
| $C_{iss}$    | $V_{GS} = 0\text{V}$ , $V_{DS} = -25\text{V}$ , $f = 1\text{MHz}$   |                       | 2845 | pF        |
| $C_{oss}$    |   |                       | 1015 | pF        |
| $C_{rss}$    |   |                       | 275  | pF        |
| $t_{d(on)}$  | <b>Resistive Switching Times</b><br>$V_{GS} = -10\text{V}$ , $V_{DS} = 0.5 \cdot V_{DSS}$ , $I_D = 0.5 \cdot I_{D25}$<br>$R_G = 3.3\Omega$ (External) |                       | 22   | ns        |
| $t_r$        |   |                       | 29   | ns        |
| $t_{d(off)}$ |   |                       | 38   | ns        |
| $t_f$        |   |                       | 22   | ns        |
| $Q_{g(on)}$  | $V_{GS} = -10\text{V}$ , $V_{DS} = 0.5 \cdot V_{DSS}$ , $I_D = 0.5 \cdot I_{D25}$   |                       | 60   | nC        |
| $Q_{gs}$     |   |                       | 17   | nC        |
| $Q_{gd}$     |   |                       | 23   | nC        |
| $R_{thJC}$   |   |                       |      | 0.42 °C/W |
| $R_{thCS}$   | (TO-3P)(TO-247)   |                       | 0.21 | °C/W      |
|              | (TO-220)  |                       | 0.50 | °C/W      |

#### Source-Drain Diode

| Symbol   | Test Conditions<br>( $T_J = 25^\circ\text{C}$ , Unless Otherwise Specified)                             | Characteristic Values |       |               |
|----------|---|-----------------------|-------|---------------|
|          |   | Min.                  | Typ.  | Max.          |
| $I_S$    | $V_{GS} = 0\text{V}$  |                       |       | - 52 A        |
| $I_{SM}$ | Repetitive, Pulse Width Limited by $T_{JM}$   |                       |       | - 200 A       |
| $V_{SD}$ | $I_F = -26\text{A}$ , $V_{GS} = 0\text{V}$ , Note 1   |                       |       | - 3.5 V       |
| $t_{rr}$ | $I_F = -26\text{A}$ , $-di/dt = -100\text{A}/\mu\text{s}$<br>$V_R = -50\text{V}$ , $V_{GS} = 0\text{V}$ |                       | 120   | ns            |
| $Q_{RM}$ |   |                       | 0.53  | $\mu\text{C}$ |
| $I_{RM}$ |   |                       | - 8.9 | A             |

Note 1: Pulse test,  $t \leq 300\mu\text{s}$ , duty cycle,  $d \leq 2\%$ .

IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.

IXYS MOSFETs and IGBTs are covered by one or more of the following U.S. patents:

|           |           |           |           |              |              |              |              |              |             |
|-----------|-----------|-----------|-----------|--------------|--------------|--------------|--------------|--------------|-------------|
| 4,835,592 | 4,931,844 | 5,049,961 | 5,237,481 | 6,162,665    | 6,404,065 B1 | 6,683,344    | 6,727,585    | 7,005,734 B2 | 7,157,338B2 |
| 4,860,072 | 5,017,508 | 5,063,307 | 5,381,025 | 6,259,123 B1 | 6,534,343    | 6,710,405 B2 | 6,759,692    | 7,063,975 B2 |             |
| 4,881,106 | 5,034,796 | 5,187,117 | 5,486,715 | 6,306,728 B1 | 6,583,505    | 6,710,463    | 6,771,478 B2 | 7,071,537    |             |

### TO-247 Outline




| SYM | INCHES   |      | MILLIMETERS |       |
|-----|----------|------|-------------|-------|
|     | MIN      | MAX  | MIN         | MAX   |
| A   | .185     | .209 | 4.7         | 5.3   |
| A1  | .087     | .102 | 2.2         | 2.54  |
| A2  | .059     | .098 | 2.2         | 2.6   |
| b   | .040     | .055 | 1.0         | 1.4   |
| b1  | .065     | .084 | 1.65        | 2.13  |
| b2  | .113     | .123 | 2.87        | 3.12  |
| C   | .016     | .031 | .4          | .8    |
| D   | .819     | .845 | 20.80       | 21.46 |
| E   | .610     | .640 | 15.75       | 16.26 |
| e   | .215 BSC |      | 5.45 BSC    |       |
| L   | .780     | .800 | 19.81       | 20.32 |
| L1  | .177     |      | 4.50        |       |
| ∅P  | .140     | .144 | 3.55        | 3.65  |
| Q   | .212     | .244 | 5.4         | 6.2   |
| R   | .170     | .216 | 4.32        | 5.49  |
| S   | .242 BSC |      | 6.15 BSC    |       |

### TO-220 Outline



| SYM | INCHES   |      | MILLIMETERS |       |
|-----|----------|------|-------------|-------|
|     | MIN      | MAX  | MIN         | MAX   |
| A   | .170     | .190 | 4.32        | 4.83  |
| b   | .025     | .040 | 0.64        | 1.02  |
| b1  | .045     | .065 | 1.15        | 1.65  |
| c   | .014     | .022 | 0.35        | 0.56  |
| D   | .580     | .630 | 14.73       | 16.00 |
| E   | .390     | .420 | 9.91        | 10.66 |
| e   | .100 BSC |      | 2.54 BSC    |       |
| F   | .045     | .055 | 1.14        | 1.40  |
| H1  | .230     | .270 | 5.85        | 6.85  |
| J1  | .090     | .110 | 2.29        | 2.79  |
| k   | 0        | .015 | 0           | 0.38  |
| L   | .500     | .550 | 12.70       | 13.97 |
| L1  | .110     | .230 | 2.79        | 5.84  |
| ∅P  | .139     | .161 | 3.53        | 4.08  |
| Q   | .100     | .125 | 2.54        | 3.18  |


### TO-3P Outline



| SYM | INCHES   |      | MILLIMETERS |       |
|-----|----------|------|-------------|-------|
|     | MIN      | MAX  | MIN         | MAX   |
| A   | .185     | .193 | 4.70        | 4.90  |
| A1  | .051     | .059 | 1.30        | 1.50  |
| A2  | .057     | .065 | 1.45        | 1.65  |
| b   | .035     | .045 | 0.90        | 1.15  |
| b2  | .075     | .087 | 1.90        | 2.20  |
| b4  | .114     | .126 | 2.90        | 3.20  |
| c   | .022     | .031 | 0.55        | 0.80  |
| D   | .780     | .791 | 19.80       | 20.10 |
| D1  | .665     | .677 | 16.90       | 17.20 |
| E   | .610     | .622 | 15.50       | 15.80 |
| E1  | .531     | .539 | 13.50       | 13.70 |
| e   | .215 BSC |      | 5.45 BSC    |       |
| L   | .779     | .795 | 19.80       | 20.20 |
| L1  | .134     | .142 | 3.40        | 3.60  |
| ∅P  | .126     | .134 | 3.20        | 3.40  |
| ∅P1 | .272     | .280 | 6.90        | 7.10  |
| S   | .193     | .201 | 4.90        | 5.10  |

All metal area are tin plated.

### TO-263 Outline



| SYM | INCHES   |      | MILLIMETERS |       |
|-----|----------|------|-------------|-------|
|     | MIN      | MAX  | MIN         | MAX   |
| A   | .160     | .190 | 4.06        | 4.83  |
| A1  | .080     | .110 | 2.03        | 2.79  |
| b   | .020     | .039 | 0.51        | 0.99  |
| b2  | .045     | .055 | 1.14        | 1.40  |
| c   | .016     | .029 | 0.40        | 0.74  |
| c2  | .045     | .055 | 1.14        | 1.40  |
| D   | .340     | .380 | 8.64        | 9.65  |
| D1  | .315     | .350 | 8.00        | 8.89  |
| E   | .380     | .410 | 9.65        | 10.41 |
| E1  | .245     | .320 | 6.22        | 8.13  |
| e   | .100 BSC |      | 2.54 BSC    |       |
| L   | .575     | .625 | 14.61       | 15.88 |
| L1  | .090     | .110 | 2.29        | 2.79  |
| L2  | .040     | .055 | 1.02        | 1.40  |
| L3  | .050     | .070 | 1.27        | 1.78  |
| L4  | 0        | .005 | 0           | 0.13  |

Fig. 1. Output Characteristics @  $T_J = 25^\circ\text{C}$




Fig. 2. Extended Output Characteristics @  $T_J = 25^\circ\text{C}$




Fig. 3. Output Characteristics @  $T_J = 125^\circ\text{C}$




Fig. 4.  $R_{DS(on)}$  Normalized to  $I_D = -26\text{A}$  Value vs. Junction Temperature




Fig. 5.  $R_{DS(on)}$  Normalized to  $I_D = -26\text{A}$  Value vs. Drain Current




Fig. 6. Maximum Drain Current vs. Case Temperature




Fig. 7. Input Admittance




Fig. 8. Transconductance




Fig. 9. Forward Voltage Drop of Intrinsic Diode




Fig. 10. Gate Charge




Fig. 11. Capacitance




Fig. 12. Forward-Bias Safe Operating Area





Fig. 13. Maximum Transient Thermal Impedance





---

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics).