


0.020" ± 0.002" DIAMETER,  
24 AWG, TINNED CCS,  
1.0" LONG MINIMUM



RESISTANCE @ +25°C = 2,500 Ω ± 5%  
RESISTANCE/TEMPERATURE CURVE = "F"  
BETA "β" (0 TO +50°C) = 3,419°K NOMINAL  
TEMPERATURE COEFFICIENT @ +25°C = -3.86%/°C NOMINAL  
DISSIPATION CONSTANT = 2 mW/°C NOMINAL (STILL AIR)  
THERMAL TIME CONSTANT = 5 SECONDS NOMINAL (STILL AIR)  
THERMAL TIME CONSTANT = 0.5 SECONDS NOMINAL (STIRRED OIL)  
MAXIMUM TEMPERATURE RATING = +300°C

---	ISO RELEASE	12/15/03	DD
"A"	LEAD WIRE WAS 0.020" ± 0.001" DIAMETER & 1.125" LONG NOMINAL	12/15/03	DD
REV	REVISION RECORD	DATE	APP

SCALE NONE	U.S. SENSOR CORP. © COPYRIGHT 714-639-1000 www.ussensor.com NTC THERMISTOR P/N 252FG1J
DRAWN BY C. PAYAN	
DATE 06/15/99	
REV. "A"	
LAYER 0 OF 1	