



RESISTANCE @ +25°C = 10,000 Ω ± 10%
 RESISTANCE/TEMPERATURE CURVE = "E1"
 BETA "β" (+25 TO +85°C) = 3,435°K NOMINAL
 TEMPERATURE COEFFICIENT @ +25°C = -3.52%/°C NOMINAL
 DISSIPATION CONSTANT = 0.45 mW/°C NOMINAL (AIR)
 THERMAL TIME CONSTANT = 2.5 SECONDS NOMINAL (AIR)
 MAXIMUM TEMPERATURE RATING = +260°C

SEE MANUFACTURING SPECIFICATION (LAYER 1)

| | | | |
|------|-----------------------|----------|-----|
| NONE | RELEASE TO PRODUCTION | 04/03/14 | DD |
| REV | REVISION RECORD | DATE | APP |

| | | |
|----------|-------------|---|
| SCALE | NONE | U.S. SENSOR CORP. © COPYRIGHT 714-639-1000 www.ussensor.com NTC THERMISTOR P/N GT103E1K |
| DRAWN BY | DAN DANKERT | |
| DATE | 04/03/14 | |
| REV. | NONE | |
| LAYER | 0 OF 2 | |