

Thyristor \ Diode Module

$$V_{RRM} = 2 \times 1600 \text{ V}$$


$$I_{TAV} = 550 \text{ A}$$

$$V_T = 1.27 \text{ V}$$

Phase leg + NTC


Part number

MCMA550PD1600PTSF



Backside: isolated

 E72873



Features / Advantages:

- Thyristor for line frequency
- Planar passivated chip
- Long-term stability
- Direct Copper Bonded Al₂O₃-ceramic

Applications:

- Line rectifying 50/60 Hz
- Softstart AC motor control
- DC Motor control
- Power converter
- AC power control
- Lighting and temperature control

Package: SimBus F


- Isolation Voltage: 4300 V~
- Industry standard outline
- RoHS compliant
- PressFit-Pins for PCB mounting
- Height: 17 mm
- Base plate: Copper internally DCB isolated
- Advanced power cycling
- Phase Change Material available

Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.

Rectifier				Ratings			
Symbol	Definition	Conditions		min.	typ.	max.	Unit
$V_{RSM/DSM}$	max. non-repetitive reverse/forward blocking voltage					1700	V
$V_{RRM/DRM}$	max. repetitive reverse/forward blocking voltage					1600	V
I_{RD}	reverse current, drain current	$V_{R/D} = 1600$ V	$T_{VJ} = 25^{\circ}\text{C}$			400	μA
		$V_{R/D} = 1600$ V	$T_{VJ} = 140^{\circ}\text{C}$			30	mA
V_T	forward voltage drop	$I_T = 550$ A	$T_{VJ} = 25^{\circ}\text{C}$			1.29	V
		$I_T = 1100$ A				1.66	V
		$I_T = 550$ A	$T_{VJ} = 125^{\circ}\text{C}$			1.27	V
		$I_T = 1100$ A				1.72	V
I_{TAV}	average forward current	$T_C = 85^{\circ}\text{C}$	$T_{VJ} = 140^{\circ}\text{C}$			550	A
$I_{T(RMS)}$	RMS forward current	sine 180° $d = 0.5$				865	A
V_{T0}	threshold voltage					0.82	V
r_T	slope resistance	} for power loss calculation only				0.8	m Ω
R_{thJC}	thermal resistance junction to case					0.05	K/W
R_{thCH}	thermal resistance case to heatsink				0.03		K/W
P_{tot}	total power dissipation			$T_C = 25^{\circ}\text{C}$		1150	W
I_{TSM}	max. forward surge current	$t = 10$ ms; (50 Hz), sine	$T_{VJ} = 45^{\circ}\text{C}$			13.0	kA
		$t = 8,3$ ms; (60 Hz), sine	$V_R = 0$ V			14.0	kA
		$t = 10$ ms; (50 Hz), sine	$T_{VJ} = 140^{\circ}\text{C}$			11.1	kA
		$t = 8,3$ ms; (60 Hz), sine	$V_R = 0$ V			11.9	kA
I^2t	value for fusing	$t = 10$ ms; (50 Hz), sine	$T_{VJ} = 45^{\circ}\text{C}$			845.0	kA ² s
		$t = 8,3$ ms; (60 Hz), sine	$V_R = 0$ V			820.0	kA ² s
		$t = 10$ ms; (50 Hz), sine	$T_{VJ} = 140^{\circ}\text{C}$			610.5	kA ² s
		$t = 8,3$ ms; (60 Hz), sine	$V_R = 0$ V			592.6	kA ² s
C_J	junction capacitance	$V_R = 400$ V $f = 1$ MHz	$T_{VJ} = 25^{\circ}\text{C}$		647		pF
P_{GM}	max. gate power dissipation	$t_p = 30$ μs	$T_C = 140^{\circ}\text{C}$			240	W
		$t_p = 300$ μs				120	W
P_{GAV}	average gate power dissipation					40	W
$(di/dt)_{cr}$	critical rate of rise of current	$T_{VJ} = 140^{\circ}\text{C}; f = 50$ Hz repetitive, $I_T = 1650$ A				100	A/ μs
		$t_p = 200$ $\mu\text{s}; di_G/dt = 0.45$ A/ $\mu\text{s}; I_G = 0.45$ A; $V = \frac{2}{3} V_{DRM}$ non-repet., $I_T = 550$ A				500	A/ μs
$(dv/dt)_{cr}$	critical rate of rise of voltage	$V = \frac{2}{3} V_{DRM}$	$T_{VJ} = 140^{\circ}\text{C}$			1000	V/ μs
		$R_{GK} = \infty$; method 1 (linear voltage rise)					
V_{GT}	gate trigger voltage	$V_D = 6$ V	$T_{VJ} = 25^{\circ}\text{C}$			2	V
			$T_{VJ} = -40^{\circ}\text{C}$			3	V
I_{GT}	gate trigger current	$V_D = 6$ V	$T_{VJ} = 25^{\circ}\text{C}$			300	mA
			$T_{VJ} = -40^{\circ}\text{C}$			440	mA
V_{GD}	gate non-trigger voltage	$V_D = \frac{2}{3} V_{DRM}$	$T_{VJ} = 140^{\circ}\text{C}$			0.25	V
I_{GD}	gate non-trigger current					20	mA
I_L	latching current	$t_p = 30$ μs	$T_{VJ} = 25^{\circ}\text{C}$			400	mA
		$I_G = 0.45$ A; $di_G/dt = 0.45$ A/ μs					
I_H	holding current	$V_D = 6$ V $R_{GK} = \infty$	$T_{VJ} = 25^{\circ}\text{C}$			300	mA
t_{gd}	gate controlled delay time	$V_D = \frac{1}{2} V_{DRM}$	$T_{VJ} = 25^{\circ}\text{C}$			2	μs
		$I_G = 0.5$ A; $di_G/dt = 0.5$ A/ μs					
t_q	turn-off time	$V_R = 100$ V; $I_T = 550$ A; $V = \frac{2}{3} V_{DRM}$ $T_{VJ} = 125^{\circ}\text{C}$			300		μs
		$di/dt = 10$ A/ μs $dv/dt = 50$ V/ μs $t_p = 200$ μs					

Package SimBus F		Ratings				
Symbol	Definition	Conditions	min.	typ.	max.	Unit
I_{RMS}	RMS current	per terminal			tbd	A
T_{VJ}	virtual junction temperature		-40		140	°C
T_{op}	operation temperature		-40		125	°C
T_{stg}	storage temperature		-40		125	°C
Weight				350		g
M_D	mounting torque		3		6	Nm
M_T	terminal torque		3		6	Nm
$d_{Spp/App}$	creepage distance on surface striking distance through air	terminal to terminal	13.3	10.0		mm
$d_{Spb/Apb}$		terminal to backside	10.2	10.2		mm
V_{ISOL}	isolation voltage	t = 1 second	4300			V
		t = 1 minute	3600			V


Part description


M = Module
 C = Thyristor (SCR)
 M = Thyristor
 A = (up to 1800V)
 550 = Current Rating [A]
 PD = Phase leg
 1600 = Reverse Voltage [V]
 PT = PressFit-Pin, Thermistor
 SF = SimBus F
 - = Hyphen
 PC = Phase Change Material

Ordering	Ordering Number	Marking on Product	Delivery Mode	Quantity	Code No.
Standard	MCMA550PD1600PTSF	MCMA550PD1600PTSF	Blister	24	520868
Alternative	MCMA550PD1600PTSF-PC	MCMA550PD1600PTSF	Blister	24	


Similar Part	Package	Voltage class
MCMA280PD1600PTSF	SimBus F	1600
MCMA400PD1600PTSF	SimBus F	1600

Temperature Sensor NTC

Symbol	Definition	Conditions	min.	typ.	max.	Unit
R_{25}	resistance	$T_{VJ} = 25^\circ$	4.85	5	5.15	kΩ
$B_{25/50}$	temperature coefficient			3375		K


Equivalent Circuits for Simulation
** on die level*
 $T_{VJ} = 140^\circ\text{C}$

Thyristor

$V_{0\max}$	threshold voltage	0.82				V
$R_{0\max}$	slope resistance *	0.28				mΩ





Outlines SimBus F




Bemerkung / Note:

- Nichttolerierete Maße nach / Measure w/o tolerances acc. DIN ISO 2768-T1-m
- PCB-Lochmuster / PCB hole pattern: see pin position
- Toleranz Pin-Position und PCB-Lochmuster / Tolerance of pin position and PCB hole pattern: $\oplus 0.1$
- Bohrlochdurchmesser / Diameter of drill: $\varnothing 1.16$ mm
- Endlochdurchmesser / Diameter of plated holes: $\varnothing 1.00 - 1.10$ mm (Cu thickness in via typ. 50 µm)
- Beschichtung / Plating: chem. Sn max. 15 µm
- Einpresskraft / Insert Force: per terminal with a typ. insert speed of 1 mm/s: typ. 90 N
- Weitere Angaben / Further information: www.ixys.com Application note IXAN0077
- Montageanleitung / Mounting instruction: www.ixys.com Application note IXAN0024

Detail A: PCB-Montage / Mounting on PCB^L

- Empfohlene, selbstschneidende Schraube / Recommended, self-tapping screw: **EJOT PT®** (Größe / size: **K25**)^L
- Max. Schraubenlänge / Max. screw length: **PCB-Dicke / thickness + 6 mm** (max. Lochtiefe / hole depth)^L
- Empfohlenes Drehmoment / Recommended mounting torque: **1.5 Nm**




Thyristor


Fig. 1 Forward characteristics





 Fig. 2 Surge overload current
 I_{TSM} : crest value, t : duration

 Fig. 3 I^2t versus time (1-10 s)


Fig. 4 Gate voltage & gate current




 Fig. 5 Gate controlled delay time t_{gd}


Fig. 6 Max. forward current at case temperature




 Fig. 7a Power dissipation versus direct output current
 Fig. 7b and ambient temperature


Fig. 8 Transient thermal impedance junction to case