


Specification Status: Released

Maximum Electrical

Rating
Operating Voltage: 12Vdc
Interrupt Current: 100A
 Chip Size: 5 X 12mm
 Leads: Nickel 1/4H
 0.125mm nominal thickness
 Solder: Lead-free
 Tape: Polyester (White)
 13 mm nominal width



Marking: (Color: Green)
 ———— Manufacturer's Mark
 ✕ R23 ——— Part Identification
 □ □ □ □ ——— Lot Identification

TABLE I. DIMENSIONS:

	A		B		C		D		E		F	
	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX
mm:	20.9	23.1	4.9	5.3	---	0.8	4.1	5.8	4.1	5.8	3.9	4.1
in*:	(0.82)	(0.91)	(0.19)	(0.21)	--	(0.03)	(0.16)	(0.23)	(0.16)	(0.23)	(0.15)	(0.16)

*Rounded off approximation

TABLE II. PERFORMANCE RATINGS: As measured in Mueller Kelvin Clips model BU-75K.

I HOLD	CURRENT TRIP LIMITS								TIME TO TRIP		REFERENCE RESISTANCE E		ONE-HOUR POST-TRIP RESISTANCE E		TRIPPED-STATE POWER DISSIPATION	
	AMPS 25°C	AMPS AT 0°C	AMPS AT 25°C	AMPS AT 60°C	AMPS AT -°C	SECONDS AT 25°C, 10.0A	SECONDS AT 25°C, 10.0A	OHMS AT 25°C	OHMS AT 25°C	WATTS AT 25°C, 12V	WATTS AT 25°C, 12V					
HOLD	HOLD	TRIP	HOLD	TRIP	HOLD	TRIP	HOLD	TRIP	TYP	MAX	MIN	MAX	TYP	MAX	TYP	MAX
2.3	3.4	6.6	2.3	5.0	0.9	2.3	---	---	2.4	5	0.012	0.018	0.031	0.036	1.4	2.5

Agency Recognitions: UL, TUV, CSA
 Reference Documents: PS300
 Precedence: This specification takes precedence over documents referenced herein.
 Effectivity: Reference documents shall be the issue in effect on the date of invitation for bid.
 CAUTION: Operation beyond the rated voltage or current may result in rupture, electrical arcing or flame.

Materials Information:

ROHS Compliant **ELV Compliant** **Pb-Free**
 Directive 2002/95/EC Compliant Directive 2000/53/EC Compliant



Expertise Applied | Answers Delivered

PolySwitch®
PTC Devices
Overcurrent Protection Device

PRODUCT: VLR230F

DOCUMENT: SCD25580
PCN: D03587
REV LETTER: D
REV DATE: July 26, 2016
PAGE NO.: 2 OF 2

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, military, aerospace, medical, lifesaving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.